



Main

Range	Prisma
Range compatibility	Prisma P
Product or component type	Mounting plate
Accessory / separate part category	Installation accessory
Installed device	<p>Easypact : fixed EZC400 - control: toggle - vertical installation</p> <p>Easypact : fixed CVS400 without earth leakage protection - control: toggle - vertical installation</p> <p>Easypact : fixed CVS630 without earth leakage protection - control: toggle - vertical installation</p> <p>Compact : fixed INS320...400 - control: direct front rotary handle - vertical installation</p> <p>Compact : fixed INS500...630 - control: direct front rotary handle - vertical installation</p> <p>Compact : fixed INV320...400 - control: direct front rotary handle - vertical installation</p> <p>Compact : fixed INV500...630 - control: direct front rotary handle - vertical installation</p> <p>Compact : fixed NSX400 without earth leakage protection - control: toggle - vertical installation</p> <p>Compact : fixed NSX630 without earth leakage protection - control: toggle - vertical installation</p> <p>Compact : plug-in NSX400 without earth leakage protection - control: toggle - vertical installation</p> <p>Compact : plug-in NSX630 without earth leakage protection - control: toggle - vertical installation</p> <p>Compact : drawout NSX400 without earth leakage protection - control: toggle - vertical installation</p> <p>Compact : drawout NSX630 without earth leakage protection - control: toggle - vertical installation</p> <p>Compact : fixed NSX400 without earth leakage protection - control: direct front rotary handle - vertical installation</p> <p>Compact : fixed NSX630 without earth leakage protection - control: direct front rotary handle - vertical installation</p> <p>Compact : plug-in NSX400 without earth leakage protection - control: direct front rotary handle - vertical installation</p> <p>Compact : plug-in NSX630 without earth leakage protection - control: direct front rotary handle - vertical installation</p> <p>Compact : drawout NSX400 without earth leakage protection - control: direct front rotary handle - vertical installation</p> <p>Compact : drawout NSX630 without earth leakage protection - control: direct front rotary handle - vertical installation</p> <p>Compact : fixed NSX400 without earth leakage protection - control: motor mechanism - vertical installation</p> <p>Compact : fixed NSX630 without earth leakage protection - control: motor mechanism - vertical installation</p> <p>Compact : plug-in NSX400 without earth leakage protection - control: motor mechanism - vertical installation</p> <p>Compact : plug-in NSX630 without earth leakage protection - control: motor mechanism - vertical installation</p>

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Compact : drawout NSX400 without earth leakage protection - control: motor mechanism - vertical installation
 Compact : drawout NSX630 without earth leakage protection - control: motor mechanism - vertical installation
 Easycompact : fixed CVS400 without earth leakage protection - control: direct front rotary handle - vertical installation
 Easycompact : fixed CVS630 without earth leakage protection - control: direct front rotary handle - vertical installation
 Easycompact : fixed CVS400 with earth leakage protection - control: toggle - vertical installation
 Easycompact : fixed CVS630 with earth leakage protection - control: toggle - vertical installation
 Compact : fixed NSX400 with earth leakage protection - control: toggle - vertical installation
 Compact : fixed NSX630 with earth leakage protection - control: toggle - vertical installation
 Compact : plug-in NSX400 with earth leakage protection - control: toggle - vertical installation
 Compact : plug-in NSX630 with earth leakage protection - control: toggle - vertical installation
 Compact : drawout NSX400 with earth leakage protection - control: toggle - vertical installation
 Compact : drawout NSX630 with earth leakage protection - control: toggle - vertical installation
 Compact : fixed NSX400 with earth leakage protection - control: direct front rotary handle - vertical installation
 Compact : fixed NSX630 with earth leakage protection - control: direct front rotary handle - vertical installation
 Compact : plug-in NSX400 with earth leakage protection - control: direct front rotary handle - vertical installation
 Compact : plug-in NSX630 with earth leakage protection - control: direct front rotary handle - vertical installation
 Compact : drawout NSX400 with earth leakage protection - control: direct front rotary handle - vertical installation
 Compact : drawout NSX630 with earth leakage protection - control: direct front rotary handle - vertical installation
 Compact : drawout NSX400 with earth leakage protection - control: motor mechanism - vertical installation
 Compact : drawout NSX630 with earth leakage protection - control: motor mechanism - vertical installation
 Easycompact : fixed CVS400 with earth leakage protection - control: direct front rotary handle - vertical installation
 Easycompact : fixed CVS630 with earth leakage protection - control: direct front rotary handle - vertical installation
 Easycompact : fixed EZC630 - control: toggle - vertical installation

Poles description

1 x 3P : fixed : NSX400 vertical installation
 1 x 3P : fixed : NSX630 vertical installation
 1 x 3P : fixed : EZC400 vertical installation
 1 x 3P : fixed : EZC630 vertical installation
 1 x 3P : fixed : CVS400 vertical installation
 1 x 3P : fixed : CVS630 vertical installation
 1 x 3P : fixed : INS320...400 vertical installation
 1 x 3P : fixed : INS500...630 vertical installation
 1 x 3P : fixed : INV320...400 vertical installation
 1 x 3P : fixed : INV500...630 vertical installation
 1 x 4P : fixed : NSX400 vertical installation
 1 x 4P : fixed : NSX630 vertical installation
 1 x 4P : fixed : EZC400 vertical installation
 1 x 4P : fixed : EZC630 vertical installation
 1 x 4P : fixed : CVS400 vertical installation
 1 x 4P : fixed : CVS630 vertical installation
 1 x 4P : fixed : INS320...400 vertical installation
 1 x 4P : fixed : INS500...630 vertical installation
 1 x 4P : fixed : INV320...400 vertical installation
 1 x 4P : fixed : INV500...630 vertical installation
 1 x 3P : drawout : NSX400 vertical installation
 1 x 3P : drawout : NSX630 vertical installation
 2 x 3P : drawout : NSX400 vertical installation
 2 x 3P : drawout : NSX630 vertical installation
 2 x 3P : fixed : NSX400 vertical installation
 2 x 3P : fixed : NSX630 vertical installation
 2 x 3P : fixed : CVS630 vertical installation
 1 x 3P : plug-in : NSX400 vertical installation
 1 x 3P : plug-in : NSX630 vertical installation
 2 x 3P : plug-in : NSX400 vertical installation
 2 x 3P : plug-in : NSX630 vertical installation
 1 x 4P : drawout : NSX400 vertical installation
 1 x 4P : drawout : NSX630 vertical installation
 2 x 4P : drawout : NSX400 vertical installation
 2 x 4P : drawout : NSX630 vertical installation
 2 x 4P : fixed : NSX400 vertical installation
 2 x 4P : fixed : NSX630 vertical installation
 2 x 4P : fixed : CVS630 vertical installation
 1 x 4P : plug-in : NSX400 vertical installation

1 x 4P : plug-in : NSX630 vertical installation
 2 x 4P : plug-in : NSX400 vertical installation
 2 x 4P : plug-in : NSX630 vertical installation
 2 x 3P : fixed : CVS400 vertical installation
 2 x 4P : fixed : CVS400 vertical installation

Complementary

Installation description	Cubicle - width 650 mm, depth 400 mm
Number of vertical modules [50 mm]	13 module(s) : CVS400 without earth leakage protection , direct in 650 mm Wide cubicle 13 module(s) : CVS630 without earth leakage protection , direct in 650 mm Wide cubicle 13 module(s) : EZC400, direct in 650 mm Wide cubicle 13 module(s) : EZC630, direct in 650 mm Wide cubicle 10 module(s) : INS320...400, direct in 650 mm Wide cubicle 11 module(s) : INS500...630, direct in 650 mm Wide cubicle 10 module(s) : INV320...400, direct in 650 mm Wide cubicle 11 module(s) : INV500...630, direct in 650 mm Wide cubicle 11 module(s) : NSX400 without earth leakage protection , direct in 650 mm Wide cubicle 13 module(s) : NSX630 without earth leakage protection , direct in 650 mm Wide cubicle 15 module(s) : CVS400 with earth leakage protection , direct in 650 mm Wide cubicle 13 module(s) : CVS400 with earth leakage protection , direct in 650 mm Wide cubicle 15 module(s) : CVS630 with earth leakage protection , direct in 650 mm Wide cubicle 13 module(s) : CVS630 with earth leakage protection , direct in 650 mm Wide cubicle 13 module(s) : NSX400 with earth leakage protection , direct in 650 mm Wide cubicle 15 module(s) : NSX630 with earth leakage protection , direct in 650 mm Wide cubicle
Height	372 mm
Product weight	5.08 kg
Surface finish	Matt Smooth
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White RAL 9001

Environment

Standards	IEC 61439-2
Product certifications	ASEFA

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0807 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Available End of Life Information

Contractual warranty

Warranty period	18 months
-----------------	-----------