


# Product data sheet

Specifications



## FRONT PLATE NSX/NSX VIGI(ELCB)+POWERTAG HZ TOGGLE/ROTARY HANDLE L600 4M

03334

! Discontinued

! Discontinued on: Apr 25, 2023

### Main

Range	Prisma
Range Of Product	Prisma G
Product Or Component Type	Front plate
Accessory / Separate Part Category	Installation accessory
Range Compatibility	Prisma Prisma G enclosure
Type Of Front Plate	Cut-out
Installed Device	ComPact: fixed NSX100...250 without earth leakage protection - control: toggle - horizontal installation ComPact: fixed NSX100...250 without earth leakage protection - control: direct front rotary handle - horizontal installation
Poles Description	1 x 3P: mounting plate support: NSX100...250 horizontal installation 1 x 4P: mounting plate support: NSX100...250 horizontal installation
Operating Position	Horizontal

### Complementary

Enclosure/Cubicle Description	Floor-standing enclosure + duct - width 600 + 300 mm Wall-mounted enclosure + duct - width 600 + 300 mm Floor-standing enclosure - width 600 mm Wall-mounted enclosure - width 600 mm
Connection Position	Direct connection Connection block
Number Of Vertical Modules [50 Mm]	4
Standards	IEC 61439-2 IEC 61439-1
Product Certifications	ASEFA
Material	Steel
Surface Finish	Smooth Matt
Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9001)
Height	199 mm
Width	499 mm
Quantity Per Set	Set of 1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Functional Unit	600 + 300 mm Prisma G floor-standing enclosure + duct ComPact NSX100...250 without fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 4
	600 + 300 mm Prisma G floor-standing enclosure + duct ComPact NSX100...250 without fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 4
	600 + 300 mm Prisma G floor-standing enclosure + duct ComPact NSX100...250 without fixed toggle horizontal 3P 1 direct with long terminal shield 4
	600 + 300 mm Prisma G floor-standing enclosure + duct ComPact NSX100...250 without fixed toggle horizontal 4P 1 direct with long terminal shield 4
	600 + 300 mm Prisma G wall-mounted enclosure + duct ComPact without fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 4
	600 + 300 mm Prisma G wall-mounted enclosure + duct ComPact without fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 4
	600 + 300 mm Prisma G wall-mounted enclosure + duct ComPact without fixed toggle horizontal 3P 1 direct with long terminal shield 4
	600 + 300 mm Prisma G wall-mounted enclosure + duct ComPact without fixed toggle horizontal 4P 1 direct with long terminal shield 4

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.000 cm
Package 1 Width	21.500 cm
Package 1 Length	52.000 cm
Package 1 Weight	808.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	17.000 cm
Package 2 Width	22.500 cm
Package 2 Length	52.500 cm
Package 2 Weight	8.290 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	90
Package 3 Height	36.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	86.610 kg

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

## Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
-------------------	---

China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
-----------------------	---

Environmental Disclosure	<a href="#">Product Environmental Profile</a>
--------------------------	---