



Main

Range	Prisma
Range compatibility	Prisma P
Product or component type	Front plate
Accessory / separate part category	Installation accessory
Type of front plate	Cut-out
Installed device	<p>Compact : fixed NSX100...160 without earth leakage protection - control: direct front rotary handle - horizontal installation</p> <p>Compact : fixed NSX250 without earth leakage protection - control: direct front rotary handle - horizontal installation</p> <p>Compact : fixed NSX100...160 without earth leakage protection - control: toggle - horizontal installation</p> <p>Compact : fixed NSX250 without earth leakage protection - control: toggle - horizontal installation</p> <p>Easypact : fixed CVS100...160 without earth leakage protection - control: direct front rotary handle - horizontal installation</p> <p>Easypact : fixed CVS250 without earth leakage protection - control: direct front rotary handle - horizontal installation</p> <p>Compact : fixed NSX100...160 without earth leakage protection - control: motor mechanism - horizontal installation</p> <p>Compact : fixed NSX250 without earth leakage protection - control: motor mechanism - horizontal installation</p> <p>Compact : plug-in NSX100...160 without earth leakage protection - control: toggle - horizontal installation</p> <p>Compact : plug-in NSX250 without earth leakage protection - control: toggle - horizontal installation</p> <p>Compact : fixed NSX100...160 with earth leakage protection - control: toggle - horizontal installation</p> <p>Compact : fixed NSX250 with earth leakage protection - control: toggle - horizontal installation</p> <p>Compact : fixed NSX100...160 with earth leakage protection - control: direct front rotary handle - horizontal installation</p> <p>Compact : fixed NSX250 with earth leakage protection - control: direct front rotary handle - horizontal installation</p> <p>Easypact : fixed CVS100...160 with earth leakage protection - control: direct front rotary handle - horizontal installation</p> <p>Easypact : fixed CVS250 with earth leakage protection - control: direct front rotary handle - horizontal installation</p> <p>Compact : fixed NSX100...160 with earth leakage protection - control: motor mechanism - horizontal installation</p> <p>Compact : fixed NSX250 with earth leakage protection - control: motor mechanism - horizontal installation</p>

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Compact : plug-in NSX100...160 without earth leakage protection - control: direct front rotary handle - horizontal installation
 Compact : plug-in NSX250 without earth leakage protection - control: direct front rotary handle - horizontal installation
 Compact : plug-in NSX100...160 with earth leakage protection - control: direct front rotary handle - horizontal installation
 Compact : plug-in NSX250 with earth leakage protection - control: direct front rotary handle - horizontal installation
 Compact : plug-in NSX100...160 without earth leakage protection - control: motor mechanism - horizontal installation
 Compact : plug-in NSX250 without earth leakage protection - control: motor mechanism - horizontal installation
 Compact : plug-in NSX100...160 with earth leakage protection - control: motor mechanism - horizontal installation
 Compact : plug-in NSX250 with earth leakage protection - control: motor mechanism - horizontal installation
 Compact : plug-in NSX100...160 with earth leakage protection - control: toggle - horizontal installation
 Compact : plug-in NSX250 with earth leakage protection - control: toggle - horizontal installation
 Enerlin'X : fixed FDM121 - control: remote control - vertical installation

Poles description	1 x 3P : mounting plate support : CVS100...160 horizontal installation 1 x 3P : mounting plate support : CVS250 horizontal installation 1 x 3P : mounting plate support : NSX100...160 horizontal installation 1 x 3P : mounting plate support : NSX250 horizontal installation
Operating position	Horizontal

Complementary

Enclosure/Cubicle description	Cubicle - width 650 mm, depth 400 mm
Connection position	Direct connection
Number of vertical modules [50 mm]	3
Standards	IEC 61439-1 IEC 61439-2
Product certifications	ASEFA
Quantity per set	Set of 1
Height	150 mm
Product weight	0.62 kg
Surface finish	Smooth Matt
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White RAL 9001

Environment

IK degree of protection	IK07 conforming to EN/IEC 62262
-------------------------	---------------------------------

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0750 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Available End of Life Information

Contractual warranty

Warranty period	18 months
-----------------	-----------