


Product data sheet

Specifications



100 METALLIC SPACER THICK. 5MM LINERGY BS

04669

 **Discontinued on:** Apr 25, 2023

 **Discontinued**

Main

Range	Linergy
Range Of Product	Linergy BS
Product Or Component Type	Wedge
Accessory / Separate Part Category	Busbar accessory
Range Compatibility	Prisma Prisma P enclosure Linergy Linergy BS busbar
Product Destination	Busbar

Complementary

Quantity Per Set	Set of 100
Height	25 mm
Width	45.5 mm
Depth	5 mm
Net Weight	3.98 kg
Colour	Natural

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.5 cm
Package 1 Width	10.0 cm
Package 1 Length	15.5 cm
Package 1 Weight	3.98 kg
Unit Type Of Package 2	S02
Number Of Units In Package 2	2
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	8.24 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

✓ Halogen Free Plastic Parts Product

Certifications & Standards

Eu Rohs Directive [Compliant](#)
[EU RoHS Declaration](#)

China Rohs Regulation [China RoHS declaration](#)
Pro-active China RoHS declaration (out of China RoHS legal scope)

Environmental Disclosure [Product Environmental Profile](#)

Circularity Profile [End of Life Information](#)