



### Main

Range	Linergy
Product name	Linergy BS
IP degree of protection	IPxx B
Product or component type	Distribution block
Product compatibility	Spacial enclosures

### Complementary

Mounting support	Plain backplate Slotted backplate Prisma upright
Mounting mode	Horizontal Vertical
Poles description	4P
[Ue] rated operational voltage	440 V AC
[Ui] rated insulation voltage	750 V AC
[Uimp] rated impulse withstand voltage	8 kV
[Ie] rated operational current	400 A
[Icw] rated short-time withstand current	20 kA 1 s
[Ipk] rated peak withstand current	40 kA
I <sup>2</sup> t on activation	400000000 A <sup>2</sup> .s
Busbar cross section	32 x 5 mm
Connections - terminals	Supply : crimped lug 50 mm <sup>2</sup> Supply : flexible bars, 32 x 5 mm Distribution : M6 holes (phase) , 13 x 1...50 mm <sup>2</sup>
Height	235 mm
Width	470 mm
Depth	115 mm
Product weight	4.2 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Environment

Standards	IEC 61439-2 EN/IEC 61439-1
Product certifications	ASEFA

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0812 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available <a href="#">Product Environmental Profile</a>
Product end of life instructions	Need no specific recycling operations

## Contractual warranty

Warranty period	18 months
-----------------	-----------