



Main

Range	Prisma
Product or component type	Interface and connection Canalis
Accessory / separate part category	Interface accessory

Complementary

Cubicle-device connection	KT with Canalis
Poles description	3P
Installation description	Cubicle - width 650 mm
Cubicle depth	400 mm : front 400 + 400 mm : rear
Installed device	Compact : drawout NS630b...1000 - control: direct front rotary handle vertical installation Compact : drawout NS1250 - control: direct front rotary handle vertical installation Compact : drawout NS630b...1000 - control: motor mechanism vertical installation Compact : drawout NS1250 - control: motor mechanism vertical installation Compact : drawout NS630b...1000 - control: toggle vertical installation Compact : drawout NS1250 - control: toggle vertical installation Compact : fixed NS630b...1000 - control: toggle vertical installation Compact : fixed NS1250 - control: toggle vertical installation Compact : fixed NS630b...1000 - control: direct front rotary handle vertical installation Compact : fixed NS1250 - control: direct front rotary handle vertical installation Compact : fixed NS630b...1000 - control: motor mechanism vertical installation Compact : fixed NS1250 - control: motor mechanism vertical installation Compact : fixed NS1600 - control: toggle vertical installation Compact : fixed NS1600 - control: direct front rotary handle vertical installation Compact : fixed NS1600 - control: motor mechanism vertical installation Compact : drawout NS1600 - control: direct front rotary handle vertical installation Compact : drawout NS1600 - control: motor mechanism vertical installation Compact : drawout NS1600 - control: toggle vertical installation Masterpact : fixed NT06...10 - control: toggle vertical installation Masterpact : fixed NT06...10 - control: motor mechanism vertical installation Masterpact : fixed NT12 - control: toggle vertical installation Masterpact : fixed NT12 - control: motor mechanism vertical installation Masterpact : fixed NT16 - control: toggle vertical installation Masterpact : fixed NT16 - control: motor mechanism vertical installation
[I _e] rated operational current	1600 A
Quantity per set	Set of 1
Height	410 mm
Width	600 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Depth	285 mm
Product weight	27.2 kg
Colour	Stainless steel

Environment

Standards	IEC 61439-2 IEC 61439-1
Product certifications	ASEFA

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0925 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Available End of Life Information

Contractual warranty

Warranty period	18 months
-----------------	-----------