



Main

Range	Linergy
Product name	Linergy BW
IP degree of protection	IPxx B
Product or component type	Power supply block
Accessory / separate part category	Current distribution accessory
Provided equipment	With connection

Complementary

Cubicle-device connection	Linergy BW busbar
Poles description	4P
Installation description	<p>Cubicle - width 650 mm</p> <p>Floor-standing enclosure - width 600 mm</p> <p>Wall-mounted enclosure - width 600 mm</p> <p>Floor-standing enclosure - width 850 mm</p> <p>Pack enclosure - width 600 mm</p> <p>Floor-standing enclosure + duct - width 600 + 300 mm</p> <p>Wall-mounted enclosure + duct - width 600 + 300 mm</p>
Installed device	<p>Compact : fixed NSX100...160 with earth leakage protection - control: toggle horizontal installation</p> <p>Compact : fixed NSX250 with earth leakage protection - control: toggle horizontal installation</p> <p>Compact : fixed INS250 - control: direct front rotary handle horizontal installation</p> <p>Compact : fixed INS250 - control: direct front rotary handle vertical installation</p> <p>Easypact : fixed CVS100...160 without earth leakage protection - control: toggle horizontal installation</p> <p>Easypact : fixed CVS250 without earth leakage protection - control: toggle horizontal installation</p> <p>Compact : fixed INV250 - control: direct front rotary handle horizontal installation</p> <p>Compact : fixed INV100 - control: direct front rotary handle horizontal installation</p> <p>Compact : fixed INV250 - control: direct front rotary handle vertical installation</p> <p>Compact : plug-in NSX100...160 without earth leakage protection - control: toggle horizontal installation</p> <p>Compact : plug-in NSX250 without earth leakage protection - control: toggle horizontal installation</p> <p>Compact : fixed NSX100...160 without earth leakage protection - control: toggle horizontal installation</p> <p>Compact : fixed NSX250 without earth leakage protection - control: toggle horizontal installation</p> <p>Compact : fixed NSX100...160 without earth leakage protection - control: direct front rotary handle horizontal installation</p> <p>Compact : fixed NSX250 without earth leakage protection - control: direct front rotary handle horizontal installation</p>

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Compact : fixed NSX100...250 and ammeter without earth leakage protection - control: toggle horizontal installation
 Easycompact : fixed CVS100...160 with earth leakage protection - control: toggle horizontal installation
 Easycompact : fixed CVS250 with earth leakage protection - control: toggle horizontal installation
 Compact : fixed NSX100...160 with earth leakage protection - control: direct front rotary handle horizontal installation
 Compact : fixed NSX250 with earth leakage protection - control: direct front rotary handle horizontal installation
 Compact : fixed INV100 - control: direct front rotary handle vertical installation
 Compact : fixed INV250 - control: lateral handle vertical installation
 Compact : fixed NSX100...160 without earth leakage protection - control: motor mechanism horizontal installation
 Compact : fixed NSX250 without earth leakage protection - control: motor mechanism horizontal installation
 Compact : fixed INS250 - control: lateral handle vertical installation
 Compact : fixed INV200 - control: direct front rotary handle vertical installation
 Compact : fixed INV160 - control: direct front rotary handle horizontal installation
 Compact : fixed INV160 - control: direct front rotary handle vertical installation
 Compact : fixed INV200 - control: direct front rotary handle horizontal installation

[Ie] rated operational current	250 A
Quantity per set	Set of 1
Product weight	1.18 kg

Environment

Standards	IEC 61439-1, inside Prisma IEC 61439-2, inside Prisma
Product certifications	ASEFA

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0812 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------