


# Product data sheet

Specifications



## LINERGY BS MULTISTAGE B.BAR SUPPORT 630A

04192

 **Discontinued on:** Jan 20, 2022

 **Discontinued**

### Main

|                           |  |
|---------------------------|--|
| Range                     | Linergy  |
| Range Of Product          | Linergy  |
| Product Or Component Type | Busbar support   |
| Product Name              | Linergy BS   |
| Range Compatibility       | Linergy Linergy BS busbar<br>Prisma Prisma G enclosure |

### Complementary

|   |  |
|---|--|
| Cubicle-Device Connection                             | Linergy BS lateral busbar  |
| Installation Description                              | Floor-standing duct - width 300 mm<br>Wall-mounted duct - width 300 mm   |
| Permissible Current                                   | 160 A - busbar cross section: 15 x 5 mm<br>250 A - busbar cross section: 20 x 5 mm<br>400 A - busbar cross section: 32 x 5 mm<br>630 A - busbar cross section: 32 x 8 mm   |
| [I <sub>cw</sub> ] Rated Short-Time Withstand Current | 10 kA (1 s) at 160 A for 450 mm between support centres<br>20 kA (1 s) at 400 A for 300 mm between support centres<br>13 kA (1 s) at 250 A for 450 mm between support centres<br>15 kA (1 s) at 400 A for 450 mm between support centres<br>15 kA (1 s) at 630 A for 450 mm between support centres<br>20 kA (1 s) at 630 A for 300 mm between support centres<br>25 kA (0.6 s) at 400 A for 300 mm between support centres<br>25 kA (1 s) at 630 A for 300 mm between support centres |
| Quantity Per Set                                      | Set of 1   |
| Net Weight  | 0.2 kg   |

### Environment

|                        |                            |
|------------------------|----------------------------|
| Standards              | IEC 61439-1<br>IEC 61439-2 |
| Product Certifications | ASEFA                      |

### Packing Units

|                              |         |
|------------------------------|---------|
| Unit Type Of Package 1       | PCE     |
| Number Of Units In Package 1 | 1       |
| Package 1 Height             | 2 cm    |
| Package 1 Width              | 11.5 cm |
| Package 1 Length             | 23.5 cm |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

---

|                  |       |
|------------------|-------|
| Package 1 Weight | 200 g |
|------------------|-------|

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

## Certifications & Standards

|                   |   |
|-------------------|---|
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope)<br><a href="#">EU RoHS Declaration</a> |
|-------------------|---|

|                       |   |
|-----------------------|---|
| China Rohs Regulation | <a href="#">China RoHS declaration</a><br>Pro-active China RoHS declaration (out of China RoHS legal scope) |
|-----------------------|---|

|                          |   |
|--------------------------|---|
| Environmental Disclosure | <a href="#">Product Environmental Profile</a> |
|--------------------------|---|