



Main

Range of product	Thorsman
Product or component type	Wall plug
Device short name	TP
Provided equipment	Without screw
Device application	Lightweight installation
Drilling diameter	5.5 mm brick 5.5 mm concrete
Drilling depth	≥ 20 mm
Screw diameter	3.5...5 mm
Material	PEHD (polyethylene high density)

Complementary

Practical load capacity	0.3 kN shear solid brick 4.5 0.4 kN shear concrete C25 4.5 0.15 kN pull-out load concrete C25 6 0.15 kN pull-out load solid brick 6
Practical load capacity	40 kg shear concrete 4.5 15 kg pull-out load concrete 6 30 kg shear solid brick 4.5 15 kg pull-out load solid brick 6
Colour tint	White
Ambient air temperature for operation	-50...80 °C
Diameter	5.5 mm
Length	16.5 mm

Environment

Quantity per set	Set of 100
Sale per indivisible quantity	10
Product weight	0.0004 kg

Contractual warranty

Warranty period	18 months
-----------------	-----------