

Product data sheet

Specifications



Thorsman - TCP 0 - clip plug - without screw - set of 100

1140003

Main

| | |
|---------------------------|---------------------|
| Range Of Product | Thorsman |
| Product Or Component Type | Clip plug |
| Device Short Name | TCP |
| Device Application | Cable clip and nail |
| Drilling Diameter | 5.5 mm |
| Minimum Drilling Depth | 20 mm |
| Nail Diameter | 1.2...3 mm |
| Material | PS (polystyrene) |

Complementary

| | |
|---------------------------------------|-------------|
| Colour Tint | White |
| Ambient Air Temperature For Operation | -40...70 °C |
| Diameter | 7.5 mm |
| Length | 18 mm |

Environment

| | |
|-------------------------------|------------|
| Quantity Per Set | Set of 100 |
| Sale Per Indivisible Quantity | 1 |
| Net Weight | 0.0005 kg |

Packing Units

| | |
|------------------------------|-----------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 0.100 cm |
| Package 1 Width | 0.750 cm |
| Package 1 Length | 1.800 cm |
| Package 1 Weight | 0.500 g |
| Unit Type Of Package 2 | BB1 |
| Number Of Units In Package 2 | 100 |
| Package 2 Height | 3.000 cm |
| Package 2 Width | 4.800 cm |
| Package 2 Length | 17.800 cm |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|------------------|----------|
| Package 2 Weight | 56.000 g |
|------------------|----------|

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

| | | |
|---|----------------------------|-----|
| ✓ | Reach Free Of Svhc | |
| ✓ | Toxic Heavy Metal Free | |
| ✓ | Mercury Free | |
| ✓ | Rohs Exemption Information | Yes |

Certifications & Standards

| | |
|--------------------------|---|
| Reach Regulation | REACH Declaration |
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |