



### Main

|                                    |  |
|------------------------------------|--|
| Range                              | Prisma   |
| Product name                       | Prisma G   |
| IP degree of protection            | IP40 with door<br>IP30 without door<br>IP41 with door and canopy<br>IP43 with door, canopy and IP43 gasket |
| Product or component type          | Duct   |
| Enclosure type                     | Functional enclosure delivered in kit form   |
| Device application                 | Low voltage electrical distribution  |
| Enclosure mounting                 | Surface  |
| Type of front plate                | Without (to be ordered separately)   |
| Product compatibility              | Floor-standing enclosure - width 600 mm  |
| Number of vertical modules [50 mm] | 27   |
| Number of 18 mm modules per row    | 10   |

### Complementary

|  |  |
|--|--|
| Installation description                 | Floor-standing duct - width 300 mm                     |
| [Ui] rated insulation voltage            | 1000 V on main rear busbars conforming to IEC 61439-2  |
| [In] rated current                       | 630 A at 40 °C conforming to IEC 61439-2               |
| [Icw] rated short-time withstand current | 25 kA (1 s) conforming to IEC 61439-2                  |
| [Ipk] rated peak withstand current       | 53 kA conforming to IEC 61439-2                        |
| Network frequency                        | 50/60 Hz   |
| Enclosure material                       | Enclosure : treated sheet steel                        |
| Additional information                   | Can be combined side by side and one on top of another |
| Quantity per set                         | Set of 1   |
| Height                                   | 1530 mm, with plinth                                   |
| Width                                    | 300 mm   |
| Depth                                    | 205 mm   |
| Product weight                           | 12.72 kg   |

|                |                |
|----------------|----------------|
| Surface finish | Matt<br>Smooth |
| Colour         | White RAL 9001 |

## Environment

|                         |  |
|-------------------------|--|
| IK degree of protection | IK07 without door conforming to EN/IEC 62262<br>IK08 with door       |
| Protective treatment    | Electrophoresis treatment and hot-polymerised polyester epoxy powder |
| Standards               | IEC 62208<br>IEC 61439-2<br>IEC 61439-1                              |
| Mechanical robustness   | Seismic tests : 2.5G conforming to IEC 60068-2-57                    |

## Offer Sustainability

|                                  |   |
|----------------------------------|---|
| Sustainable offer status         | Green Premium product   |
| RoHS (date code: YYWW)           | Compliant - since 1809 - Schneider Electric declaration of conformity<br><a href="#">Schneider Electric declaration of conformity</a> |
| REACH                            | Reference not containing SVHC above the threshold<br><a href="#">Reference not containing SVHC above the threshold</a>                |
| Product environmental profile    | Available<br><a href="#">Product Environmental Profile</a>  |
| Product end of life instructions | Need no specific recycling operations   |

## Contractual warranty

|                 |           |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|