

# Product data sheet

Specifications



## Thorsman - TP 0 - wall plug - without screw - set of 100

1000009

### Main

Range Of Product	Thorsman
Product Or Component Type	Wall plug
Device Short Name	TP
Device Application	Lightweight installation
Drilling Diameter	5.5 mm concrete 5.5 mm brick
Minimum Drilling Depth	20 mm
Screw Diameter	3.5...5 mm
Material	PEHD (polyethylene high density)

### Complementary

Practical Load Capacity	Shear: 0.4 kN for concrete C25 4.5) Pull-out load: 0.15 kN for concrete C25 6) Shear: 0.3 kN for solid brick 4.5) Pull-out load: 0.15 kN for solid brick 6)
Practical Load Capacity	Shear: 40 kg for concrete 4.5) Pull-out load: 15 kg for concrete 6) Shear: 30 kg for solid brick 4.5) Pull-out load: 15 kg for solid brick 6)
Colour Tint	White
Ambient Air Temperature For Operation	-50...80 °C
Diameter	5.5 mm
Length	16.5 mm

### Environment

Quantity Per Set	Set of 100
Sale Per Indivisible Quantity	10
Net Weight	0.0004 kg

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.500 cm
Package 1 Width	0.500 cm
Package 1 Length	1.700 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Weight	0.400 g
------------------	---------

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations