

# Product data sheet

Specifications



Enclosure for modular device,  
Mureva Enclosure, 3x18 modules,  
without terminal block

10345

## Main

Range	Mureva
Product Name	Mureva Enclosure
Product Or Component Type	Weatherproof enclosure
Enclosure Type	Enclosure for modular device
Mounting Plate Description	Without mounting plate

## Complementary

Enclosure Mounting	Surface
Number Of 18 Mm Modules Per Row	18
Total Number Of 18 Mm Modules	54
Number Of Horizontal Rows	3
Electrical Insulation Class	Class II Double insulation
Provided Equipment	3 marking kit 3 wiring strap
Type Of Front Cover	Transparent Reversible
Power Dissipation In W	65 W
[In] Rated Current	125 A
Type Of Rail	DIN
Locking Options Description	Optional keylock
Enclosure Material	Self-extinguishing polymer
Width	448 mm
Height	610 mm
Depth	160 mm
Internal Depth	88 mm
Colour	Door: transparent green Enclosure: light grey (RAL 7035)
Targeted Country	Italy

## Environment

Standards	IEC 61439-3 IEC 60670 IEC 60695-2-1
-----------	---

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Fire Resistance	650 °C conforming to IEC 60695-2-1
Ip Degree Of Protection	IP65 conforming to IEC 60529
Ik Degree Of Protection	IK09 conforming to EN 50102
Environmental Characteristics (Uv)	UV resistant: class 3 conforming to ISO 4582:2010 Ultraviolet degradation test conforming to ISO 4892-2:2013
Overvoltage Category	II
Ambient Air Temperature For Operation	-25...60 °C

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	16.800 cm
Package 1 Width	59.400 cm
Package 1 Length	46.400 cm
Package 1 Weight	5.145 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	19
Package 2 Height	120.000 cm
Package 2 Width	80.000 cm
Package 2 Length	77.000 cm
Package 2 Weight	109755.000 kg

## Contractual warranty

Warranty	18 months
----------	-----------

# Sustainability

**Green Premium™** label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.


[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)




Lower Impact Materials   Transparency   RoHS/REACH

## Resource performance

 Minimum Percentage Of Recycled Plastic Content   26

## Well-being performance

 Rohs Exemption Information   [Yes](#)

 Halogen Free Product

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations