

Product data sheet

Specifications



Acti9 - IH - mechanical time switch - 24 h - without memory

15335

Main

Range Of Product	Acti9
Product Name	Acti9 IH
Device Short Name	IH
Product Or Component Type	Mechanical time switch
Number Of Channels	1
Function Available	Manual time changeover

Complementary

Device Application	Building
Load Type	Parallel-corrected fluorescent tube 5 x 58 W 4.7 µF Parallel-corrected fluorescent tube 7 x 40 W 7 µF Parallel-corrected fluorescent tube 2 x 100 W 18 µF 230 V AC halogen lamp 1000 W 230 V AC incandescent lamp 1000 W Fluocompact lamp 700 VA Compact fluorescent lamp 150 W LED lamp < 2 W 30 W LED lamp > 2 W 300 W
Cycle Duration	24 h
Maximum Number Of Switchings	48 on - 48 off
Minimum Interval Duration	15 min
Type Of Setting	Manual time changeover
Measurement Accuracy	+/- 1 s/day 20 °C
Power Consumption In W	0.5 W
Maximum Switching Current	16 A - 250 V AC pf = 1 4 A - 250 V AC pf = 0.6
[Ue] Rated Operational Voltage	230 V AC at 50 Hz
Mounting Support	DIN rail
9 Mm Pitches	2
Colour Tint	White (RAL 9003)
Connections - Terminals	Screw terminals
Width	18 mm
Height	90 mm
Depth	66 mm
Net Weight	0.097 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

Ambient Air Temperature For Operation	-25...50 °C
Ip Degree Of Protection	Terminals: IP20 B

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.100 cm
Package 1 Width	7.100 cm
Package 1 Length	9.900 cm
Package 1 Weight	82.0 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	100
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	8.695 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information