

# Product data sheet

## Characteristics

# 15533

extension ETL - 2P - 1C/O + 1NO - 16A - coil  
12VDC - 24VAC 50/60Hz



### Main

Product or component type	Extension for impulse relay
Device short name	ETL
Relay application	Remote control
Poles description	2P
Pole contact composition	1 C/O + 1 NO
[In] rated current	16 A
Network type	AC

### Complementary

Network frequency	50/60 Hz
[Ue] rated operational voltage	250 V AC 50/60 Hz
Control type	Remote control Toggle
Control signal type	Impulse
Switching frequency	5 switching operations/minute
Impulse duration	50 ms
Remote control type	Illuminated push-button 3 mA
Local signalling	ON/OFF indication
[Uc] control circuit voltage	12 V DC 24 V AC 50/60 Hz
Supply inrush power	19 VA
Mounting mode	Fixed, on right side of TL
Mounting support	35 mm symmetrical DIN rail
9 mm pitches	2
Height	84 mm
Width	18 mm
Depth	60 mm
Colour	Grey
Electrical durability	AC-22 : 100000 cycles AC-21 : 200000 cycles
Connections - terminals	Tunnel type terminals <= 10 mm <sup>2</sup>
Auxiliary connection terminal	Control circuit : tunnel type terminals 0.5...6 mm <sup>2</sup>

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Environment

Standards	EN 669-1 EN 669-2-2
Product certifications	CEBEC GOST IMQ NF VDE
Noise level	<= 60 dB
Tropicalisation	2
Relative humidity	95 % ( 55 °C )
Ambient air temperature for operation	-20...50 °C

## Contractual warranty

Warranty period	18 months
-----------------	-----------

## 15533 is replaced by:



electrical auxiliaries A9C32116

extension iETL iTL 16 - 2P - 1C/O + 1NO - 16A - coil 12VDC - 24VAC 50/60Hz

Qty 1

Reason for Substitution: End of life | Substitution date: 01 January 2011