



Main

Range of product	Acti 9
Product name	Acti 9 IHP
Device short name	IHP
Product or component type	Programmable digital time switch
Device application	Building
Battery type	Lithium
Number of channels	1
Language	Danish Dutch English Finnish French Norwegian Swedish
Colour tint	White (RAL 9003)

Complementary

Product compatibility	Mechanical compatibility with electrical distribution comb busbars
Power consumption in VA	3 VA
Maximum switching current	16 A - 250 V AC pf = 1 4 A - 250 V AC pf = 0.6
[Ue] rated operational voltage	230 V AC +/- 10 % at 50/60 Hz
Number of inputs	1 input(s) impulse and maintained
Accuracy	+/- 1 s/day 20 °C
Cycle duration	24 hours + 7 days
Maximum number of switchings	42
Minimum interval duration	1 min
Display type	Backlit LCD
Battery life	5 yr

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Backup time	3 years time and program saving
9 mm pitches	2
Width	18 mm
Height	85 mm
Depth	66 mm
Product weight	0.09 kg
Function	Pulse programming and random function
Absence for holidays	Yes
Time changeover	Automatic
Updated by	None
Compatibility code	IHP

Environment

Ambient air temperature for operation	-10...50 °C
IP degree of protection	IP20 B

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant Schneider Electric declaration of conformity
REACH	Reference contains SVHC above the threshold Go to CaP for more details
Product environmental profile	Available
Product end of life instructions	Available

Contractual warranty

Warranty period	18 months
-----------------	-----------