

Product data sheet

Specifications



Mini Pragma L flush enclosure - IP 30 - 1 x 12 modules - reversible front cover

10676

 **Discontinued on:** Feb 13, 2019

 **Discontinued**

Main

Range	Mini Pragma
Product Or Component Type	Enclosure
Enclosure Type	Distribution enclosure
Nb Of 18 Mm Modules Per Row	12
Nb Of Horizontal Rows	1
Provided Equipment	1 marking kit
Type Of Door	Reversible
Width	285 mm
Height	185 mm
Depth	93 mm

Complementary

Enclosure Mounting	Flush
9 Mm Pitches	24
Total Number Of 18 Mm Modules	13
Type Of Rail	DIN
Enclosure Material	Enclosure: self-extinguishing material
Colour	Enclosure: white (RAL 9003)

Environment

Standards	EN 50102 IEC 60529 IEC 60439-3 IEC 23-48 IEC 60695-2-1 EN 60439-3
Product Certifications	IMQ
Fire Resistance	650 °C (30 s) conforming to IEC 60695-2-1
Ik Degree Of Protection	IK07 conforming to EN 50102

Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile