



Main

Range	PowerLogic
Device short name	AMP
Product or component type	Ammeter
Device application	Motor
Range compatibility	Prisma G door Prisma P door
Technology type	Ferromagnetic
Scale type	80 mm over 90°
Mounting support	Front face

Complementary

Type of measurement	Current
Accuracy class	Class 1.5
Power consumption in VA	1.1 VA
Power consumption in VA	1.1 VA
Overload withstand	1.2 In, permanently 10 In, 5 s
Device mounting	Flush
Operating position	30°/Vertical
Width	96 mm
Height	96 mm
Depth	75 mm
Temperature drift	+/- 0.003 %/°C

Environment

Standards	IEC 60051-1 IEC 61000-4 IEC 61010-1
IP degree of protection	IP52
Ambient air temperature for operation	-25...50 °C
Reference temperature	23 °C

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0627 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------
