



Main

Range of product	Multi 9
Product name	Multi 9 PRD1
Product or component type	Surge arrester with pluggable cartridge
Device short name	PRD1 25r
Device application	Distribution
Poles description	1P + N
Remote signalling	With
Signal contacts composition	1 SD (1 C/O)
Surge arrester type	Electrical distribution network
Earthing system	TT TN-S

Complementary

Surge arrester class type	Type 1 + 2
Surge arrester technology	MOV Spark gap
[Ue] rated operational voltage	230 V AC (+/- 10 %) at 50 Hz 400 V AC (+/- 10 %) at 50 Hz
[In] nominal discharge current	Common mode: 100 kA (N/PE) Differential mode: 25 kA (L/N)
[Iimp] impulse current	Common mode: 100 kA N/PE 50 A.s Differential mode: 25 kA L/N 12.5 A.s
[Uc] maximum continuous operating voltage	Differential mode: 350 V L/N Common mode: 350 V N/PE
Maximum [Up] voltage protection level	Common mode <1.5 kV type 2 N/PE Differential mode <1.5 kV type 2 L/N
[If] follow current	25 kA differential mode L/N 0.1 kA common mode N/PE
Disconnecter device type	Associated fuse gG 315 A standard Associated circuit breaker Compact NSX100B 100 A curve C - Icu 10 kA Associated circuit breaker Compact NSX100B 100 A curve C - Icu 15 kA Associated circuit breaker Compact NSX100B 100 A curve C - Icu 25 kA
Signalling circuit voltage	1.5 A/250 V AC 50/60 Hz
Mounting mode	Clip-on

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Mounting support	DIN rail
9 mm pitches	8
Height	90 mm
Width	71.6 mm
Depth	70 mm
Net weight	0.77 kg
Colour	Anthracite grey (RAL 7016)
Material	PBT (polybutylene terephthalate)
Response time	<= 25 ns
Connections - terminals	Tunnel type terminal (downside) 2.5...35 mm ² Tunnel type terminal (upside) 2.5...35 mm ²
Tightening torque	4.5 N.m

Environment

Standards	EN 61643-11:2012 IEC 61643-11:2011
Product certifications	CE
Quality labels	KEMA-KEUR
IP degree of protection	IP40 on front face: conforming to IEC 60529 IP20 built-in: conforming to IEC 60529
IK degree of protection	IK05 conforming to IEC 62262
Relative humidity	5...90 %
Operating altitude	2000 m
Ambient air temperature for operation	-25...60 °C
Ambient air temperature for storage	-40...80 °C

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------

尺寸图

尺寸

