



### Main

Device short name	ATLc+S
Product or component type	Centralized control and remote indication auxiliary
Signal contacts composition	1 C/O
Signalling circuit voltage	24 V DC : 0.01...6 A 48 V DC : 0.01...2 A 130 V DC : 0.01...1 A 24...240 V AC : 50/60 Hz 0.01...6 A
[Uc] control circuit voltage	24...240 V AC 50/60 Hz

### Complementary

Mounting mode	Fixed, on left side of TL
Mounting support	DIN rail
9 mm pitches	2
Height	84 mm
Width	18 mm
Depth	60 mm
Colour	Grey
Connections - terminals	Input connection : tunnel type terminals for 2 flexible cable(s) 2.5 mm <sup>2</sup> Input connection : tunnel type terminals for 2 rigid cable(s) 1.5 mm <sup>2</sup> Signalling circuit : tunnel type terminals for 2 flexible cable(s) 2.5 mm <sup>2</sup> Signalling circuit : tunnel type terminals for 2 rigid cable(s) 1.5 mm <sup>2</sup> Output connection : yellow clips

### Environment

Tropicalisation	2
Relative humidity	95 % (55 °C)
Ambient air temperature for operation	-20...50 °C

### Contractual warranty

Warranty period	18 months
-----------------	-----------

15409 is replaced by:

---



electrical auxiliaries A9C15409

Acti 9 centralized control and remote indication - iATLc+s

Qty 1

Reason for Substitution: End of life | Substitution date: 01 January 2011

---