

Product data sheet

Specifications



auxiliary contact - 1 NC + 1 OC -
380..415 V - 6 A - for RCCB

16940

Main

Range Of Product	Multi9
Product Or Component Type	OC contact
Device Short Name	OFSP
Signal Contacts Composition	1 C/O 1 NC
[In] Rated Current	AC-12 3 A at 380...415 V, AC 50/60 Hz AC-12 6 A at 220...240 V, AC 50/60 Hz DC-12 1 A at 130 V, DC DC-12 1.5 A at 60 V, DC DC-12 2 A at 48 V, DC DC-12 6 A at 24 V, DC

Complementary

Mounting Mode	Fixed
Mounting Support	DIN rail
Comb Busbar And Distribution Block Compatibility	NO
Connections - Terminals	Tunnel type terminal2 cable(s) 1...1.5 mm² - flexible Tunnel type terminal2 cable(s) 1...1.5 mm² - rigid
Tightening Torque	0.8 N.m

Environment

Standards	EN/IEC 60947-5-1
Ip Degree Of Protection	IP20 conforming to EN/IEC 60947-5-1
Pollution Degree	3 conforming to EN/IEC 60947-5-1
Ambient Air Temperature For Operation	-25...50 °C
Ambient Air Temperature For Storage	-40...85 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.7 cm
Package 1 Width	8.1 cm
Package 1 Length	9.5 cm
Package 1 Weight	52.0 g
Unit Type Of Package 2	S03

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 2	45
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	2.746 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability




Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration	
Eu Rohs Directive	Compliant	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)	
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins	
Circularity Profile	No need of specific recycling operations	