



### Main

Product or component type	Impulse relay
Device short name	TL
Device application	Remote control
Poles	2P
Pole contact composition	2 NO
[In] rated current	16 A
Network type	AC
[Uc] control circuit voltage	12 V DC 24 V AC 50/60 Hz

### Complementary

Network frequency	50/60 Hz
[Ue] rated operational voltage	250 V AC 50/60 Hz
Control type	Coil disconnection Remote control
Control signal type	Impulse
Switching frequency	5 switching operations/minute 100 switching operations/day
Impulse duration	50 ms...1 s
Remote control type	Illuminated push-button 3 mA
Local signalling	ON/OFF indication
Mounting mode	Fixed
Mounting support	DIN rail
9 mm pitches	2
Height	84 mm
Width	18 mm
Depth	60 mm
Electrical durability	AC-22 : 100000 cycles AC-21 : 200000 cycles
Range compatibility	Multi 9 ATet Multi 9 ATL

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Environment

Standards	EN 669-1 EN 669-2-2
Product certifications	GOST
Quality labels	CEBEC IMQ NF VDE
Noise level	60 dB
Tropicalisation	2
Relative humidity	95 % ( 55 °C )
Ambient air temperature for operation	-20...50 °C

## Contractual warranty

Warranty period	18 months
-----------------	-----------

## 15523 is replaced by:



impulse relay A9C30112

impulse relay iTL - 2P - 2 NO - 16A - coil 12 VDC - 24 VAC 50/60Hz

Qty 1

Reason for Substitution: End of life | Substitution date: 01 January 2011