

Product data sheet

Characteristics

16030

modular analog ammeter without scale iAMP - 0..2000 A



Main

Range	Acti 9
Device short name	IAMP
Product or component type	Ammeter
Range compatibility	Prisma G door Prisma P door
Technology type	Ferromagnetic
Scale type	Pseudo-linear scale over 90°
Mounting support	DIN rail

Complementary

Type of measurement	Current
Accuracy class	Class 1.5
Power consumption in VA	1.1 VA
Power consumption in VA	1.1 VA
Overload withstand	1.2 In, permanently 10 In, 5 s
9 mm pitches	8
Width	70 mm
Height	83 mm
Depth	66 mm
Temperature drift	+/- 0.03 %/°C
Connections - terminals	Tunnel type terminal rigid 1.5...6 mm ²

Environment

Standards	IEC 60051-1 IEC 61000-4 IEC 61010-1
Ambient air temperature for operation	-25...50 °C
Reference temperature	23 °C

Offer Sustainability

RoHS (date code: YYWW)	Compliant
------------------------	-----------

 Schneider Electric declaration of conformity

REACH

Reference not containing SVHC above the threshold
Reference not containing SVHC above the threshold

Contractual warranty

Warranty period

18 months
