

Product data sheet

Specifications



selector switch CM'clac - 2 positions - 2 C/O - 20 A

16197

⚠ Discontinued on: Oct 2, 2019

⚠ Discontinued

Main

Range Of Product	DuoLine
Range	DuoLine
Product Name	DuoLine CM'clac
Product Or Component Type	Selector switch
Device Short Name	CM'clac
Device Application	Electrical circuit control
Contacts Type And Composition	2 C/O
[Ue] Rated Operational Voltage	250 V AC
Standards	EN 60669-1 EN 60947-5-1
Quality Labels	NF

Complementary

[Ie] Rated Operational Current	20 A
Control Type	Toggle 2 positions
Marking	0 - 1
Mounting Mode	Clip-on
Mounting Support	DIN rail
Comb Busbar And Distribution Block Compatibility	Upside: Bar'clac
9 Mm Pitches	4
Height	82 mm
Width	36 mm
Depth	75 mm
Electrical Durability	AC-22: 30000 cycles

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.5 cm
Package 1 Width	3.5 cm
Package 1 Length	8.5 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Weight	0.088 kg
------------------	----------

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

<div><div>✓</div><div>Reach Free Of Svhc</div></div>	
<div><div>✓</div><div>Toxic Heavy Metal Free</div></div>	
<div><div>✓</div><div>Mercury Free</div></div>	
<div><div>✓</div><div>Rohs Exemption Information</div></div>	<div>Yes</div>
<div>Eu Rohs Directive</div>	<div><div>Compliant</div><div>EU RoHS Declaration</div></div>
<div>China Rohs Regulation</div>	<div><div>China RoHS declaration</div><div>Pro-active China RoHS declaration (out of China RoHS legal scope)</div></div>
<div>Weee</div>	<div>The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins</div>