



Main

Range of product	Multi 9
Product name	Multi 9 PRD1
Product or component type	Surge arrester with pluggable cartridge
Device short name	PRD1 25r
Device application	Distribution
Poles description	3P + N
Remote signalling	With
Signal contacts composition	1 SD (1 C/O)
Surge arrester type	Electrical distribution network
Earthing system	TN-S TT

Complementary

Surge arrester class type	Type 1 + 2
Surge arrester technology	MOV Spark gap
[Ue] rated operational voltage	230 V (+/- 10 %) AC 50 Hz 400 V (+/- 10 %) AC 50 Hz
[In] nominal discharge current	Common mode : 100 kA N/PE Differential mode : 25 kA L/N
[Iimp] impulse current	Common mode : 100 kA N/PE 50 A.s Differential mode : 25 kA L/N 12.5 A.s
[Uc] maximum continuous operating voltage	Common mode : 350 V N/PE Differential mode : 350 V L/N
[Up] voltage protection level	<= 1.5 kV type 2 common mode N/PE <= 1.5 kV type 2 differential mode L/N
[If] follow current	25 kA differential mode L/N 0.1 kA common mode N/PE
Disconnecter device type	Associated fuse gG 315 A according to standard Associated circuit breaker Compact NSX100B 100 A curve C - Icu 10 kA Associated circuit breaker Compact NSX100B 100 A curve C - Icu 15 kA Associated circuit breaker Compact NSX100B 100 A curve C - Icu 25 kA
Signalling circuit voltage	1 A/250 V AC 50/60 Hz
Mounting mode	Clip-on

Mounting support	DIN rail
9 mm pitches	16
Height	90 mm
Width	142.8 mm
Depth	70 mm
Product weight	1.43 kg
Colour	Anthracite grey (RAL 7016)
Material	PBT (polybutylene terephthalate)
Response time	<= 25 ns
Connections - terminals	Tunnel type terminal, downside 2.5...35 mm ² Tunnel type terminal, upside 2.5...35 mm ²
Tightening torque	4.5 N.m

Environment

Standards	EN 61643-11 : 2012 IEC 61643-11 : 2011
Product certifications	CE
Quality labels	KEMA-KEUR
IP degree of protection	On front face : IP40 conforming to IEC 60529 Built-in : IP20 conforming to IEC 60529
IK degree of protection	IK05 conforming to IEC 62262
Relative humidity	5...90 %
Operating altitude	2000 m
Ambient air temperature for operation	-25...60 °C
Ambient air temperature for storage	-40...80 °C

Offer Sustainability

RoHS (date code: YYWW)	Compliant Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------