



Main

Range of product	Multi 9
Product or component type	Undervoltage release
Device short name	MNs
[Uc] control circuit voltage	220...240 V AC 50/60 Hz
Control type	Delayed
9 mm pitches	2
Product compatibility	C60 IDPN C120 ID DPN C60CTRL N40

Complementary

Range compatibility	Acti 9: Acti 9 iDPN Multi 9: Multi 9 N40 Multi 9: Multi 9 C60 Multi 9: Multi 9 ID
Local signalling	Action indicator
Mounting mode	Fixed
Mounting support	35 mm symmetrical DIN rail
Height	82.5 mm
Width	18 mm
Depth	68 mm
Connections - terminals	Clamp terminal 1 cable(s) 2.5 mm ² flexible Clamp terminal 1 cable(s) 2.5 mm ² rigid Clamp terminal 2 cable(s) 1.5 mm ² flexible Clamp terminal 2 cable(s) 1.5 mm ² rigid
Wire stripping length	9 mm
Tightening torque	1 N.m

Environment

Standards	EN/IEC 60947-5-1
Product certifications	ASEFA ASTA KEMA LCIE
Tropicalisation	2 conforming to EN/IEC 60947-5-1
Relative humidity	95 % at 55 °C
Ambient air temperature for operation	-25...50 °C
Ambient air temperature for storage	-40...85 °C

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available End of Life Information
Product end of life instructions	Available

Contractual warranty

Warranty period	18 months
-----------------	-----------

26963 may be replaced by any of the following products:



electrical auxiliaries A9A26963

voltage release - iMNs - tripping unit - 220..240 VAC

Qty 1

Reason for Substitution: End of life | Substitution date: 01 January 2011



electrical auxiliaries M9A26963

Multi 9 - undervoltage release - MNs - 220/240 V AC

Qty 1

Reason for Substitution: End of life | Substitution date: 01 January 2017