



Main

Range of product	NS80H-MA
Product or component type	Circuit breaker
Device short name	Compact NS80H
Circuit breaker name	Compact NS80H
Device application	Motor
Poles description	3P
Protected poles description	3t
Network type	AC
Network frequency	50/60 Hz
[In] rated current	80 A (65 °C)
[Ui] rated insulation voltage	750 V AC 50/60 Hz conforming to IEC 60947-2
[Uimp] rated impulse withstand voltage	8 kV conforming to IEC 60947-2
[Ue] rated operational voltage	690 V AC 50/60 Hz conforming to IEC 60947-2
Breaking capacity code	H
Breaking capacity	65 kA Icu at 440 V AC 50/60 Hz conforming to IEC 60947-2 70 kA Icu at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 25 kA Icu at 500 V AC 50/60 Hz conforming to IEC 60947-2 100 kA Icu at 220/240 V AC 50/60 Hz conforming to IEC 60947-2 25 kA Icu at 525 V AC 50/60 Hz conforming to IEC 60947-2 6 kA Icu at 660/690 V AC 50/60 Hz conforming to IEC 60947-2 10 kA at 600 V AC 50/60 Hz conforming to NEMA AB1 100 kA at 240 V AC 50/60 Hz conforming to NEMA AB1 65 kA at 480 V AC 50/60 Hz conforming to NEMA AB1
[Ics] rated service breaking capacity	Ics 100 kA 220/240 V AC 50/60 Hz conforming to IEC 60947-2 Ics 25 kA 500 V AC 50/60 Hz conforming to IEC 60947-2 Ics 25 kA 525 V AC 50/60 Hz conforming to IEC 60947-2 Ics 6 kA 660/690 V AC 50/60 Hz conforming to IEC 60947-2 Ics 65 kA 440 V AC 50/60 Hz conforming to IEC 60947-2 Ics 70 kA 380/415 V AC 50/60 Hz conforming to IEC 60947-2
Suitability for isolation	Yes conforming to IEC 60947-2
Utilisation category	Category A
Trip unit name	MA
Trip unit technology	Magnetic
Trip unit rating	12.5 A
Protection type	Short-circuit protection (magnetic)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Pollution degree	3 conforming to IEC 60947
------------------	---------------------------

Complementary

Control type	Toggle
Mounting mode	Fixed
Mounting support	Backplate
Upside connection	Tunnel terminal
Downside connection	Tunnel terminal
Mechanical durability	20000 cycles
Electrical durability	10000 cycles 440 V AC 50/60 Hz In/2 conforming to IEC 60947-2 7000 cycles 440 V AC 50/60 Hz In conforming to IEC 60947-2
Local signalling	Positive contact indication
Instantaneous pick-up adjustment type	Adjustable
Instantaneous pick-up adjustment range	6...14 x In
Zone selective interlocking ZSI	Without
Earth-leakage protection	Without
Height	120 mm
Width	90 mm
Depth	80 mm

Environment

Standards	IEC 60947-2
Product certifications	ASTA KEMA ASEFA LCIE
IP degree of protection	IP40 conforming to IEC 60529
IK degree of protection	IK07 conforming to EN 50102
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-50...85 °C

Contractual warranty

Warranty period	18 months
-----------------	-----------

28103 is replaced by:



Magnetic motor circuit breakers GV4LE12N

TeSys GV4 - magnetic circuit breaker - 12.5A 3P - with EverLink

Qty 1

Reason for Substitution: End of life | Substitution date: 06 January 2019