

Specifications



171CBU78090

Range Of Product	Modicon Momentum automation platform
Product Or Component Type	Processor
Integrated Connection Type	USB port

Concept	Transparent Ready class B
Web Services	Home pages Properties CPU status
Software Designation	Unity Pro
Communication Service	Modbus messaging 100 words, 200 I/O message per second
Processor Name	Spear 320s
Word Length	32 bit
Supply Voltage Limits	4.75...5.25 V
Clock Frequency	333 MHz
Topology	Multidrop Modbus
Communication Port Protocol	Modbus RS485/RS232 - 1 RJ45 19200 bps - 2-wire
Method Of Access	Master/slave
Control Parameter	CRC-16 for Modbus
Addressing	1...247 Modbus
Fail State	Safe I/O mode
Memory Description	Program memory IEC 3584 kB Program memory LL984 3584 kB
Register Words	26048
I/O Limit Processor Capacity	2048 inputs/2048 outputs
Number Of Devices	32 Modbus
Exact Time For 1 Kinstruction	83 ns
Local Signalling	1 LED (green) for processor running (RUN) 1 LED (red) for processor or system fault (ERR) 1 LED (red) for I/O module fault (I/O) 1 LED (yellow) for channel 0 operating (CH0) 1 LED (yellow) for channel 1 operating (CH1)
Marking	CE
Current Consumption	500 mA at 5 V DC
Module Format	Standard

Product Mounting	35 mm symmetrical DIN rail
Height	60.6 mm
Width	144 mm
Depth	53.47 mm
Net Weight	0.159 kg

Environment

Material	Lexan
Dielectric Strength	0 V not isolated RS485/RS232 5000 V for 1 minute RS485
Product Certifications	C-Tick FM
Standards	EN/IEC 61131-2 CSA C22.2 No 142 UL 508
Ip Degree Of Protection	IP20
Shock Resistance	15 gn during 11 ms sinusoidal vibrations
Resistance To Electrostatic Discharge	6 kV contact conforming to EN/IEC 61131-2 zone B 6 kV contact conforming to IACS E10 8 kV on air conforming to EN/IEC 61000-4-2
Resistance To Electromagnetic Fields	15 V/m 80...2700 MHz conforming to EN/IEC 61000-4-3
Ambient Air Temperature For Operation	0...60 °C
Ambient Air Temperature For Storage	-40...85 °C
Relative Humidity	5...96 %
Operating Altitude	<= 2000 m

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.500 cm
Package 1 Width	11.100 cm
Package 1 Length	20.500 cm
Package 1 Weight	236.000 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	8
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	2.374 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Reach Regulation

[REACH Declaration](#)

Eu Rohs Directive

Pro-active compliance (Product out of EU RoHS legal scope)

China Rohs Regulation

[China RoHS declaration](#)

Weee


The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

California Proposition 65

WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Dimensions Drawings

Processor and Option Adapter on a Typical Base



Mounting and Clearance

Mounting on a Wall

