

# Product data sheet

Specifications



switch disconnecter, Compact  
INS125, 125A, with red rotary  
handle and yellow front, 4 poles

28927

## Main

Range	ComPact
Product Name	ComPacT INS
Product Or Component Type	Switch disconnecter
Poles Description	4P
Network Type	DC AC
Network Frequency	50/60 Hz
[Ie] Rated Operational Current	AC-22A: 125 A AC 50/60 Hz 220/240 V AC-22A: 125 A AC 50/60 Hz 380/415 V AC-22A: 125 A AC 50/60 Hz 440/480 V 2 poles in series AC-22A: 125 A AC 50/60 Hz 500 V 2 poles in series AC-22A: 125 A AC 50/60 Hz 660/690 V 4 poles in series AC-23A: 125 A AC 50/60 Hz 220/240 V 4 poles in series AC-23A: 125 A AC 50/60 Hz 380/415 V AC-23A: 125 A AC 50/60 Hz 440/480 V AC-23A: 125 A AC 50/60 Hz 500 V AC-23A: 80 A AC 50/60 Hz 660/690 V DC-22A: 125 A DC 50/60 Hz 125 V 2 poles in series DC-23A: 125 A DC 50/60 Hz 125 V 2 poles in series DC-22A: 125 A DC 50/60 Hz 250 V 4 poles in series DC-23A: 125 A DC 50/60 Hz 250 V 4 poles in series
[Ui] Rated Insulation Voltage	750 V AC 50/60 Hz
[Uimp] Rated Impulse Withstand Voltage	8 kV
[Ith] Conventional Free Air Thermal Current	125 A at 60 °C
[Icm] Rated Short-Circuit Making Capacity	154 kA with upstream protection circuit breaker 690 V AC at 50/60 Hz 20 kA switch-disconnector alone 690 V AC at 50/60 Hz
[Ue] Rated Operational Voltage	250 V DC 690 V AC 50/60 Hz
Suitability For Isolation	Yes
Contact Position Indicator	Yes
Visible Break	No
Pollution Degree	3

## Complementary

Control Type	Rotary handle
Handle Colour	Red
Mounting Mode	Fixed
Mounting Support	Plate DIN rail

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Upside Connection	Front
Downside Connection	Front
Maximum Power	AC-23: 55 kW at 440 V AC 50/60 Hz AC-23: 37 kW at 220/240 V AC 50/60 Hz AC-23: 55 kW at 380/415 V AC 50/60 Hz AC-23: 75 kW at 500/525 V AC 50/60 Hz AC-23: 75 kW at 660/690 V AC 50/60 Hz
Rated Duty	Uninterrupted
Intermittent Duty Class	Class 120 - 60 %
Enclosure Dimensions For Ithe	260 mm x 160 mm x 55 mm
[Icw] Rated Short-Time Withstand Current	0.01 kA during 30 s conforming to IEC 60947-3 1.23 kA during 20 s conforming to IEC 60947-3 3.175 kA during 3 s conforming to IEC 60947-3 5.5 kA during 1 s conforming to IEC 60947-3
Mechanical Durability	15000 cycles
Electrical Durability	AC-22A: 1500 cycles 220/240 V AC 50/60 Hz AC-22A: 1500 cycles 380/415 V AC 50/60 Hz 4 poles in series AC-22A: 1500 cycles 440 V AC 50/60 Hz AC-22A: 1500 cycles 500 V AC 50/60 Hz AC-23A: 1500 cycles 220/240 V AC 50/60 Hz AC-23A: 1500 cycles 380/415 V AC 50/60 Hz AC-23A: 1500 cycles 440 V AC 50/60 Hz AC-23A: 1500 cycles 500 V AC 50/60 Hz DC-22A: 1500 cycles 250 V DC 50/60 Hz 4 poles in series DC-23A: 1500 cycles 250 V DC 50/60 Hz 4 poles in series AC-22A: 1500 cycles 690 V AC 50/60 Hz AC-23A: 1500 cycles 690 V AC 50/60 Hz 4 poles in series
Connection Pitch	30 mm
Height	100 mm
Width	135 mm
Depth	62.5 mm
Net Weight	0.9 kg

## Environment

Standards	IEC 60947-3 IEC 60947-1
Product Certifications	CCC KEMA-KEUR
Ip Degree Of Protection	IP40 conforming to IEC 60529
Ik Degree Of Protection	IK07 conforming to EN 50102
Ambient Air Temperature For Operation	-25...70 °C
Ambient Air Temperature For Storage	-50...85 °C

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	13.500 cm
Package 1 Width	11.500 cm
Package 1 Length	15.500 cm
Package 1 Weight	1.122 kg
Unit Type Of Package 2	S03

Number Of Units In Package 2	10
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	11.640 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™** label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	<a href="#">End of Life Information</a>