

# 29008

circuit breaker Compact NS100N - 100 A - 4 poles  
- fixed - without trip unit



ⓘ Discontinued

29008 has not been replaced. Please contact your customer care center for more information.

## Main

Range of product	NS100...250
Product or component type	Basic frame
Device short name	Compact NS100N
Circuit breaker name	Compact NS100N
Poles description	4P
Neutral position	Left
Network type	AC DC
Network frequency	50/60 Hz
Control type	Toggle
[In] rated current	100 A ( 40 °C ) 100 A ( 65 °C )
[Ui] rated insulation voltage	750 V AC 50/60 Hz conforming to IEC 60947-2
[Uimp] rated impulse withstand voltage	8 kV conforming to IEC 60947-2
[Ue] rated operational voltage	690 V AC 50/60 Hz conforming to IEC 60947-2 750 V DC conforming to IEC 60947-2
Breaking capacity code	N
Breaking capacity	10 kA at 600 V AC 50/60 Hz conforming to UL 508 25 kA at 480 V AC 50/60 Hz conforming to UL 508 35 kA at 480 V AC 50/60 Hz conforming to NEMA AB1 HIC 8 kA at 600 V AC 50/60 Hz conforming to NEMA AB1 HIC 85 kA at 240 V AC 50/60 Hz conforming to NEMA AB1 HIC 85 kA at 240 V AC 50/60 Hz conforming to UL 508 Icu 22 kA at 525 V AC 50/60 Hz conforming to IEC 60947-2 Icu 25 kA at 500 V AC 50/60 Hz conforming to IEC 60947-2 Icu 35 kA at 440 V AC 50/60 Hz conforming to IEC 60947-2 Icu 36 kA at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 Icu 8 kA at 660/690 V AC 50/60 Hz conforming to IEC 60947-2 Icu 85 kA at 220/240 V AC 50/60 Hz conforming to IEC 60947-2
[Ics] rated service breaking capacity	Ics 11 kA 525 V AC 50/60 Hz conforming to IEC 60947-2 Ics 35 kA 440 V AC 50/60 Hz conforming to IEC 60947-2 Ics 36 kA 380/415 V AC 50/60 Hz conforming to IEC 60947-2 Ics 4 kA 660/690 V AC 50/60 Hz conforming to IEC 60947-2 Ics 85 kA 220/240 V AC 50/60 Hz conforming to IEC 60947-2 Ics 12.5 kA 500 V AC 50/60 Hz conforming to IEC 60947-2
Suitability for isolation	Yes conforming to IEC 60947-2
Utilisation category	Category A
Pollution degree	3 conforming to IEC 60947

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Complementary

Mounting mode	Fixed
Mounting support	Backplate
Upside connection	Front
Downside connection	Front
Protection type	Without protection
Mechanical durability	50000 cycles conforming to IEC 60947-2
Electrical durability	30000 cycles 440 V AC 50/60 Hz In conforming to IEC 60947-2 50000 cycles 440 V AC 50/60 Hz In/2 conforming to IEC 60947-2
Connection pitch	35 mm
Height	161 mm
Width	140 mm
Depth	86 mm

## Environment

Standards	IEC 60947-2
Product certifications	ASEFA ASTA KEMA LCIE
IP degree of protection	IP40 conforming to IEC 60529
IK degree of protection	IK07 conforming to EN 50102
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-50...85 °C

## Contractual warranty

Warranty period	18 months
-----------------	-----------