

# Product data sheet

Specifications



## Thorsman - nail clip - TC 3 x 5 mm - 1.2/20/15 - clear - set of 5000

2106706

### Main

|                           |                            |
|---------------------------|----------------------------|
| Range                     | Thorsman                   |
| Range Of Product          | Thorsman                   |
| Product Or Component Type | Nail clip                  |
| Device Short Name         | TC                         |
| Device Application        | Installation of flat cable |
| Product Destination       | Flat cable 3 x 5 mm        |
| Type Of Installation      | Indoor                     |
| Provided Equipment        | Nail                       |
| Nail Diameter             | 1.2 mm                     |
| Length                    | 20 mm                      |
| Embedding Depth           | 15 mm                      |

### Complementary

|                                       |  |
|---------------------------------------|--|
| Colour Tint                           | Clear  |
| Material                              | Clip: PP (polypropylene)<br>Nail: electroplated hardened steel |
| Ambient Air Temperature For Operation | -40...80 °C  |
| Atmospheric-Corrosivity Category      | C2   |

### Environment

|                              |                                  |
|------------------------------|----------------------------------|
| Environmental Characteristic | Impact resistant<br>UV resistant |
| Quantity Per Set             | Set of 5000                      |
| Net Weight                   | 0.0003 kg                        |

### Packing Units

|                              |          |
|------------------------------|----------|
| Unit Type Of Package 1       | PCE      |
| Number Of Units In Package 1 | 1        |
| Package 1 Height             | 0.100 cm |
| Package 1 Width              | 0.600 cm |
| Package 1 Length             | 2.000 cm |
| Package 1 Weight             | 0.300 g  |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

# Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

|                          |   |
|--------------------------|---|
| Reach Regulation         | <a href="#">REACH Declaration</a>   |
| Eu Rohs Directive        | Pro-active compliance (Product out of EU RoHS legal scope)<br><a href="#">EU RoHS Declaration</a>           |
| China Rohs Regulation    | <a href="#">China RoHS declaration</a><br>Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | <a href="#">Product Environmental Profile</a>   |
| Circularity Profile      | No need of specific recycling operations  |