

# Product data sheet

Specifications



remote control source changeover,  
Transferpack, ACP plate and UA  
controller, 220 VAC to 240 VAC  
50/60 Hz

29472

## Main

Range Of Product	NSX100...250 Compact NS100...630 MasterPact NW MasterPact NT NSX400...630 Compact NS630b...1600
Product Or Component Type	Interface and control unit
Accessory / Separate Part Category	Interlocking accessory
Range Compatibility	ComPact ComPact NS circuit breaker ComPact ComPact NSX circuit breaker Masterpact MasterPact NT circuit breaker Masterpact MasterPact NW circuit breaker
Device Short Name	ACP + UA
[Us] Rated Supply Voltage	220...240 V AC at 50/60 Hz

## Complementary

Operating Mode	Automatic operation Forced operation on normal source Stop (both normal and replacement source off) Forced operation on replacement source
Interlocked Device	MasterPact NT NSX400...630 MasterPact NW NSX100...250 Compact NS100...630 Compact NS630b...1600
Selection Modes	Circuit breaker on R Circuit breaker on N
Test Function	By pressing the test button on the front of the controller
Complementary Function	Voluntary transfer to replacement source (e.g. energy management commands) Forced normal source if replacement source not operational during peak-tariff Selection of type of normal source (single-phase or three-phase) Setting of maximum startup time for the replacement source Additional contact: transfer to replacement source only if contact is closed
Local Signalling	On Off Fault trip
Input Type	Contacts customer voluntary order to transfer to source R
Output Type	Contacts customer: indication of operation in automatic or stop mode
[Ith] Conventional Free Air Thermal Current	8 A

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

[Ie] Rated Operational Current	AC-12: 4 A AC 440 V
	AC-12: 5 A AC 380/415 V
	AC-12: 8 A AC 110 V
	AC-12: 8 A AC 220/240 V
	AC-12: 8 A AC 24 V
	AC-12: 8 A AC 48 V
	AC-13: 6 A AC 110 V
	AC-13: 6 A AC 220/240 V
	AC-13: 7 A AC 24 V
	AC-13: 7 A AC 48 V
	AC-14: 4 A AC 110 V
	AC-14: 4 A AC 220/240 V
	AC-14: 5 A AC 24 V
	AC-14: 5 A AC 48 V
	AC-15: 3 A AC 220/240 V
	AC-15: 4 A AC 110 V
	AC-15: 5 A AC 24 V
	AC-15: 5 A AC 48 V
	DC-12: 0.4 A DC 250 V
	DC-12: 0.6 A DC 110 V
	DC-12: 2 A DC 48 V
	DC-12: 8 A DC 24 V
	DC-13: 2 A AC 24 V

Product Compatibility	Compact NS630b...1600
	Compact NSX100...250
	Compact NSX400...630

## Environment

Standards	IEC 947-5-1
-----------	-------------

Ip Degree Of Protection	IP20 connectors: conforming to EN 60529
	IP40 front: conforming to EN 60529
	IP30 side: conforming to EN 60529

Ik Degree Of Protection	Front: IK07 conforming to EN 50102
-------------------------	------------------------------------

## Packing Units

Unit Type Of Package 1	PCE
------------------------	-----

Number Of Units In Package 1	1
------------------------------	---

Package 1 Height	12.7 cm
------------------	---------

Package 1 Width	16.0 cm
-----------------	---------

Package 1 Length	27.5 cm
------------------	---------

Package 1 Weight	4.019 kg
------------------	----------

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance

 Mercury Free	
 Rohs Exemption Information	<a href="#">Yes</a>
Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information