

Product data sheet

Specifications



auxiliary contact - 1 NC + 1 SD NC -
for P25M - 415 V - 2.2 A

21121

Main

Range Of Product	Acti9
Product Or Component Type	OC or fault contact
Device Short Name	NC and SD
Signal Contacts Composition	2 NC
9 Mm Pitches	1

Complementary

Mounting Mode	Fixed
Mounting Support	DIN rail
Height	89 mm
Width	18 mm
Depth	65 mm
Connections - Terminals	Clamp terminal2 cable(s) 1 mm² - flexible Clamp terminal2 cable(s) 2.5 mm² - flexible Clamp terminal2 cable(s) 1 mm² - rigid

Environment

Standards	EN/IEC 60947-5-1
Product Certifications	SEMKO FIMKO NEMKO CEBEC DEMKO
Tropicalisation	2 conforming to EN/IEC 60947-5-1
Relative Humidity	95 % at 55 °C
Ambient Air Temperature For Operation	-20...60 °C
Ambient Air Temperature For Storage	-40...80 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.600 cm
Package 1 Width	1.200 cm
Package 1 Length	9.000 cm
Package 1 Weight	42.900 g

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	9.500 cm
Package 2 Width	10.000 cm
Package 2 Length	15.000 cm
Package 2 Weight	483.000 g
Unit Type Of Package 3	S03
Number Of Units In Package 3	80
Package 3 Height	30.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	4.351 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

 Toxic Heavy Metal Free	
 Mercury Free	
 Rohs Exemption Information	Yes
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations