



### Main

Product or component type	Add-on residual current devices
Device short name	Vigi C60
Poles description	2P
[In] rated current	25 A
Network type	AC
Earth-leakage sensitivity	30 mA
Earth-leakage protection time delay	Instantaneous
Earth-leakage protection class	Type AC

### Complementary

Device location in system	Outgoer
Network frequency	50/60 Hz
[Ue] rated operational voltage	220...415 V AC 50/60 Hz
Residual current tripping technology	Voltage dependent
[Ui] rated insulation voltage	500 V AC 50/60 Hz conforming to IEC 60947-2
[Uimp] rated impulse withstand voltage	6 kV conforming to IEC 60947-2
Mounting support	35 mm symmetrical DIN rail
Electrical connection to mcb	By screws
9 mm pitches	3
Height	87 mm
Width	63 mm
Depth	74 mm
Product weight	0.12 kg
Mechanical durability	20000 cycles
Connections - terminals	Tunnel type terminals flexible wire(s) 0.5...16 mm <sup>2</sup> max Tunnel type terminals rigid wire(s) 0.5...25 mm <sup>2</sup> max
Wire stripping length	14 mm

Tightening torque	2 N.m
-------------------	-------

## Environment

Standards	IEC 60947-2
Pollution degree	3 conforming to IEC 60947-2
Tropicalisation	2 conforming to IEC 60947-2
Relative humidity	95 % ( 55 °C )
Operating altitude	2000 m
Ambient air temperature for operation	-5...60 °C
Ambient air temperature for storage	-40...70 °C

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available <a href="#">Product Environmental Profile</a>
Product end of life instructions	Need no specific recycling operations <a href="#">End of Life Information</a>

## Contractual warranty

Warranty period	18 months
-----------------	-----------