



29782 has not been replaced. Please contact your customer care center for more information.

ⓘ Discontinued

### Main

Range of product	Compact NS100...630
Product or component type	Circuit breaker
Device short name	Compact NS100N
Circuit breaker name	Compact NS100N
Device application	Distribution
Poles description	4P
Protected poles description	3t 3t + N/2 4t
Neutral position	Left
Network type	AC DC
Network frequency	50/60 Hz
[In] rated current	100 A 65 °C 100 A 40 °C
[Ui] rated insulation voltage	750 V AC 50/60 Hz conforming to IEC 60947-2
[Uimp] rated impulse withstand voltage	8 kV conforming to IEC 60947-2
[Ue] rated operational voltage	690 V AC 50/60 Hz conforming to IEC 60947-2 750 V DC conforming to IEC 60947-2
Breaking capacity code	N
Breaking capacity	8 kA Icu at 660/690 V AC 50/60 Hz conforming to IEC 60947-2 22 kA Icu at 525 V AC 50/60 Hz conforming to IEC 60947-2 25 kA Icu at 500 V AC 50/60 Hz conforming to IEC 60947-2 35 kA Icu at 440 V AC 50/60 Hz conforming to IEC 60947-2 36 kA Icu at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 85 kA Icu at 220/240 V AC 50/60 Hz conforming to IEC 60947-2 10 kA at 600 V AC 50/60 Hz conforming to UL 508 25 kA at 480 V AC 50/60 Hz conforming to UL 508 35 kA at 480 V AC 50/60 Hz conforming to NEMA AB1 HIC 8 kA at 600 V AC 50/60 Hz conforming to NEMA AB1 HIC 85 kA at 240 V AC 50/60 Hz conforming to NEMA AB1 HIC 85 kA at 240 V AC 50/60 Hz conforming to UL 508
[Ics] rated service breaking capacity	Ics 11 kA 525 V AC 50/60 Hz conforming to IEC 60947-2 Ics 35 kA 440 V AC 50/60 Hz conforming to IEC 60947-2 Ics 36 kA 380/415 V AC 50/60 Hz conforming to IEC 60947-2 Ics 4 kA 660/690 V AC 50/60 Hz conforming to IEC 60947-2 Ics 85 kA 220/240 V AC 50/60 Hz conforming to IEC 60947-2 Ics 12.5 kA 500 V AC 50/60 Hz conforming to IEC 60947-2

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Utilisation category	Category A
Trip unit name	STR22SE
Trip unit technology	Electronic
Trip unit rating	36 A ( 70 °C ) 38 A ( 60 °C ) 40 A ( 20 °C )
Protection type	Instantaneous short-circuit protection Overload protection (long time) Protection of the fourth pole Short time short-circuit protection
Pollution degree	3 conforming to IEC 60947

## Complementary

Control type	Toggle
Mounting mode	Fixed
Mounting support	Backplate
Upside connection	Front
Downside connection	Front
Mechanical durability	50000 cycles
Electrical durability	30000 cycles 440 V AC 50/60 Hz In conforming to IEC 60947-2 50000 cycles 440 V AC 50/60 Hz In/2 conforming to IEC 60947-2
Connection pitch	35 mm
Local signalling	Positive contact indication
Neutral protection setting	0.5 x Ir 1 x Ir No protection
Long time pick-up adjustment type Ir	Adjustable 48 settings
Long time pick-up adjustment range	0.4...1 x In
Long time delay adjustment type	Fixed
[Tr] long-time delay adjustment range	90...180 s 1.5 x Ir 3.2...5 s 7.2 x Ir 5...7.5 s 6 x Ir
Short-time pick-up adjustment type Isd	Adjustable 8 settings
[Isd] short-time pick-up adjustment range	2...10 x Ir
Short-time delay adjustment type	Fixed
[Tsd] short-time delay adjustment range	0.04...0.06 s
Instantaneous pick-up adjustment type li	Fixed
Instantaneous pick-up adjustment range	>= 11 x In
Display type	LED
Height	161 mm
Width	140 mm
Depth	86 mm

## Environment

Standards	IEC 60947-2
Product certifications	ASEFA ASTA KEMA LCIE
IP degree of protection	IP40 conforming to IEC 60529
IK degree of protection	IK07 conforming to EN 50102
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-50...85 °C

## Contractual warranty

---

Warranty period	18 months
-----------------	-----------

---