

Product data sheet

Specifications



Auxiliary contact, Multi9, 1C/O, 1A to 6A, 220VAC to 415VAC, 24VDC to 130VDC, top connection, for RCCB only

26923

Main

Range Of Product	Multi9
Product Or Component Type	OC contact
Device Short Name	OFS
Signal Contacts Composition	1 C/O
[In] Rated Current	AC-12 3 A at 380...415 V, AC 50/60 Hz AC-12 6 A at 220...240 V, AC 50/60 Hz DC-12 1 A at 130 V, DC DC-12 1.5 A at 60 V, DC DC-12 2 A at 48 V, DC DC-12 6 A at 24 V, DC
9 Mm Pitches	1

Complementary

Mounting Mode	Fixed
Mounting Support	DIN rail
Comb Busbar And Distribution Block Compatibility	Top: YES
Height	84 mm
Width	9 mm
Depth	73 mm
Connections - Terminals	Clamp terminal2 cable(s) 1.5 mm² - flexible Clamp terminal2 cable(s) 1.5 mm² - rigid Clamp terminal1 cable(s) 0.5...2.5 mm² - flexible Clamp terminal1 cable(s) 0.5...2.5 mm² - rigid
Wire Stripping Length	9 mm
Tightening Torque	1 N.m

Environment

Standards	EN/IEC 60947-5-1 EN 62019-2
Product Certifications	NEMKO DEMKO SEMKO CEBEC FIMKO
Ip Degree Of Protection	IP20 conforming to EN/IEC 60947-5-1
Pollution Degree	3 conforming to EN/IEC 60947-5-1
Tropicalisation	2 conforming to EN/IEC 60947-5-1
Relative Humidity	95 % at 55 °C

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ambient Air Temperature For Operation	-25...50 °C
Ambient Air Temperature For Storage	-40...85 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8 cm
Package 1 Width	2 cm
Package 1 Length	9.5 cm
Package 1 Weight	43 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	12
Package 2 Height	9 cm
Package 2 Width	10 cm
Package 2 Length	25.5 cm
Package 2 Weight	584 g
Unit Type Of Package 3	S03
Number Of Units In Package 3	108
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	5.694 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability




Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

 Toxic Heavy Metal Free	
 Mercury Free	
 Rohs Exemption Information	Yes
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations