



Main

Range of product	Multi 9
Product or component type	Undervoltage release
Device short name	MN
[Uc] control circuit voltage	220...240 V AC 50/60 Hz
Control type	Standard
9 mm pitches	2
Product compatibility	C60 C60 UL489 DC C60 UL489 C60 UL1077

Complementary

Range compatibility	Multi 9: Multi 9 C60 Multi 9: Multi 9 C60H-DC
Local signalling	Action indicator
Mounting mode	Fixed
Mounting support	35 mm symmetrical DIN rail
Height	82.5 mm
Width	18 mm
Depth	68 mm
Connections - terminals	Pad terminal 1 cable(s) 2.5 mm ² flexible Pad terminal 1 cable(s) 2.5 mm ² rigid Pad terminal 2 cable(s) 1.5 mm ² flexible Pad terminal 2 cable(s) 1.5 mm ² rigid
Wire stripping length	9 mm
Tightening torque	1 N.m

Environment

Standards	EN/IEC 60947-5-1
Product certifications	ASEFA ASTA KEMA LCIE
Tropicalisation	2 conforming to EN/IEC 60947-5-1

Relative humidity	95 % at 55 °C
Ambient air temperature for operation	-25...50 °C
Ambient air temperature for storage	-40...85 °C

Contractual warranty

Warranty period	18 months
-----------------	-----------

27105 is replaced by:



electrical auxiliaries M9A26960

Multi 9 - undervoltage release - MN - 220/240 V AC - 24 V DC

Qty 1

Reason for Substitution: End of life | Substitution date: 01 January 2017