

# Product data sheet

Specifications



## voltage release - MN - 220..240 V AC

27105

⚠ Discontinued on: Mar 21, 2019

⚠ End-of-service on: Sep 22, 2020

⚠ Discontinued

### Main

Range Of Product	Multi9
Product Or Component Type	Undervoltage release
Device Short Name	MN
[Uc] Control Circuit Voltage	220...240 V AC 50/60 Hz
Control Type	Standard
9 Mm Pitches	2

### Complementary

Range Compatibility	Multi9 Multi9 C60 Multi9 Multi9 C60H-DC
Local Signalling	Action indicator
Mounting Mode	Fixed
Mounting Support	35 mm symmetrical DIN rail
Height	82.5 mm
Width	18 mm
Depth	68 mm
Connections - Terminals	Pad terminal - 1 cable(s) 2.5 mm² - flexible Pad terminal - 1 cable(s) 2.5 mm² - rigid Pad terminal - 2 cable(s) 1.5 mm² - flexible Pad terminal - 2 cable(s) 1.5 mm² - rigid
Wire Stripping Length	9 mm
Tightening Torque	1 N.m

### Environment

Standards	EN/IEC 60947-5-1
Product Certifications	KEMA ASEFA ASTA LCIE
Tropicalisation	2 conforming to EN/IEC 60947-5-1
Relative Humidity	95 % at 55 °C
Ambient Air Temperature For Operation	-25...50 °C
Ambient Air Temperature For Storage	-40...85 °C

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9 cm
Package 1 Width	2.4 cm
Package 1 Length	8 cm
Package 1 Weight	78 g

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

## Certifications & Standards

Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	<a href="#">End of Life Information</a>