

29961

circuit breaker Vigicompact NS100N - TMD - 80 A
- 4 poles 3d +N/2 - 30..10000mA



ⓘ Discontinued

29961 has not been replaced. Please contact your customer care center for more information.

Main

Range of product	Compact NS100...630
Product or component type	Circuit breaker
Device short name	Vigicompact NS100N
Circuit breaker name	Vigicompact NS100N
Device application	Distribution
Poles description	4P
Protected poles description	3t + N/2
Neutral position	Left
Network type	AC DC
Network frequency	50/60 Hz
[In] rated current	100 A 65 °C 100 A 40 °C
[Ui] rated insulation voltage	750 V AC 50/60 Hz conforming to IEC 60947-2
[Uimp] rated impulse withstand voltage	8 kV conforming to IEC 60947-2
[Ue] rated operational voltage	250 V DC conforming to IEC 60947-2 277 V AC 50/60 Hz conforming to IEC 60947-2
Breaking capacity code	N
Breaking capacity	8 kA Icu at 660/690 V AC 50/60 Hz conforming to IEC 60947-2 22 kA Icu at 525 V AC 50/60 Hz conforming to IEC 60947-2 25 kA Icu at 500 V AC 50/60 Hz conforming to IEC 60947-2 35 kA Icu at 440 V AC 50/60 Hz conforming to IEC 60947-2 36 kA Icu at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 85 kA Icu at 220/240 V AC 50/60 Hz conforming to IEC 60947-2 10 kA at 600 V AC 50/60 Hz conforming to UL 508 25 kA at 480 V AC 50/60 Hz conforming to UL 508 35 kA at 480 V AC 50/60 Hz conforming to NEMA AB1 HIC 8 kA at 600 V AC 50/60 Hz conforming to NEMA AB1 HIC 85 kA at 240 V AC 50/60 Hz conforming to NEMA AB1 HIC 85 kA at 240 V AC 50/60 Hz conforming to UL 508
[Ics] rated service breaking capacity	Ics 10 kA 600 V AC 50/60 Hz conforming to UL 508 Ics 22 kA 525 V AC 50/60 Hz conforming to IEC 60947-2 Ics 25 kA 480 V AC 50/60 Hz conforming to UL 508 Ics 25 kA 500 V AC 50/60 Hz conforming to IEC 60947-2 Ics 35 kA 440 V AC 50/60 Hz conforming to IEC 60947-2 Ics 35 kA 480 V AC 50/60 Hz conforming to NEMA AB1 HIC Ics 36 kA 380/415 V AC 50/60 Hz conforming to IEC 60947-2 Ics 8 kA 600 V AC 50/60 Hz conforming to NEMA AB1 HIC Ics 8 kA 660/690 V AC 50/60 Hz conforming to IEC 60947-2

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ics 85 kA 220/240 V AC 50/60 Hz conforming to IEC 60947-2
 Ics 85 kA 240 V AC 50/60 Hz conforming to NEMA AB1 HIC
 Ics 85 kA 240 V AC 50/60 Hz conforming to UL 508

Utilisation category	Category A
Trip unit name	TM-D
Trip unit technology	Thermal-magnetic
Trip unit rating	80 A (40 °C)
Protection type	Overload protection (thermal) Short-circuit protection (magnetic)
Earth-leakage add-on module name	MH
Earth-leakage protection	With
Pollution degree	3 conforming to IEC 60947

Complementary

Control type	Toggle
Mounting mode	Fixed
Mounting support	Backplate
Upside connection	Front
Downside connection	Front
Mechanical durability	50000 cycles
Electrical durability	30000 cycles 440 V AC 50/60 Hz In conforming to IEC 60947-2 50000 cycles 440 V AC 50/60 Hz In/2 conforming to IEC 60947-2
Connection pitch	35 mm
Local signalling	Positive contact indication
Neutral protection setting	No protection
Long time pick-up adjustment type Ir	Fixed
Long time pick-up adjustment range	0.8...1 x In
Long time delay adjustment type	Fixed
Instantaneous pick-up adjustment type li	Fixed
Instantaneous pick-up adjustment range	640 A
Earth-leakage protection class	Class A
Residual earth-leakage sensitivity adjustment type	Adjustable
[IΔn] residual earth-leakage sensitive adjustment	0.03 A 0.3 A 1 A 10 A 3 A
Residual earth-leakage time delay adjustment type	Adjustable
Height	236 mm
Width	105 mm
Depth	86 mm

Environment

Standards	IEC 60947-2
Product certifications	ASEFA ASTA KEMA LCIE
IP degree of protection	IP40 conforming to IEC 60529
IK degree of protection	IK07 conforming to EN 50102
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-50...85 °C

Contractual warranty

Warranty period	18 months
-----------------	-----------
