



Main

Range of product	NG160
Product or component type	Circuit breaker
Device short name	NG160H
Circuit breaker name	NG160H
Device application	Distribution
Poles description	4P
Protected poles description	4t
Network type	AC
Network frequency	50/60 Hz
[In] rated current	100 A (40 °C)
Breaking capacity code	H
Breaking capacity	15 kA Icu conforming to IEC 60947-2 at 500 V AC 50/60 Hz 22 kA Icu conforming to IEC 60947-2 at 440 V AC 50/60 Hz 36 kA Icu conforming to IEC 60947-2 at 380...415 V AC 50/60 Hz 50 kA Icu conforming to IEC 60947-2 at 220...240 V AC 50/60 Hz
[Ics] rated service breaking capacity	Ics 27 kA 380/415 V AC 50/60 Hz Ics 37.5 kA 220/240 V AC 50/60 Hz Ics 11.25 kA 500 V AC 50/60 Hz Ics 16.5 kA 440 V AC 50/60 Hz
Suitability for isolation	Yes
Trip unit name	TM-D
Trip unit technology	Thermal-magnetic
Trip unit rating	100 A
Protection type	Overload protection (thermal) Short-circuit protection (magnetic)

Complementary

Control type	Toggle
Mounting mode	Clipped
Mounting support	35 mm symmetrical DIN rail
Upside connection	Front
Downside connection	Front
Connections - terminals	Tunnel type terminals

Mechanical durability	10000 cycles
Electrical durability	5000 cycles 440 V
Local signalling	ON/OFF indication
Magnetic tripping current	1000 A
Long time pick-up adjustment type Ir	Fixed
Earth-leakage protection	Separate block
Height	120 mm
Width	120 mm
Depth	82.5 mm
Product compatibility	Single terminal

Environment

Standards	IEC 60947-3
-----------	-------------

Contractual warranty

Warranty period	18 months
-----------------	-----------

28652 is replaced by:



Circuit breakers LV426327

circuit breaker Compact NSXm F (36 kA at 415 VAC), 4P 4d, 100 A rating TMD trip unit, EverLink connectors

Qty 1

Reason for Substitution: End of life | Substitution date: 06 January 2019