



Main

Range of product	Compact NS100...630
Product or component type	Circuit breaker
Device short name	Compact NS250L
Circuit breaker name	Compact NS250L
Device application	Distribution
Poles description	4P
Protected poles description	3t + N/2
Neutral position	Left
Network type	AC DC
Network frequency	50/60 Hz
[In] rated current	220 A 65 °C 250 A 40 °C
[Ui] rated insulation voltage	750 V AC 50/60 Hz conforming to IEC 60947-2
[Uimp] rated impulse withstand voltage	8 kV conforming to IEC 60947-2
[Ue] rated operational voltage	690 V AC 50/60 Hz conforming to IEC 60947-2 750 V DC conforming to IEC 60947-2
Breaking capacity code	L
Breaking capacity	130 kA Icu at 440 V AC 50/60 Hz conforming to IEC 60947-2 150 kA Icu at 220/240 V AC 50/60 Hz conforming to IEC 60947-2 150 kA Icu at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 20 kA Icu at 660/690 V AC 50/60 Hz conforming to IEC 60947-2 50 kA Icu at 525 V AC 50/60 Hz conforming to IEC 60947-2 70 kA Icu at 500 V AC 50/60 Hz conforming to IEC 60947-2 130 kA at 480 V AC 50/60 Hz conforming to NEMA AB1 HIC 200 kA at 240 V AC 50/60 Hz conforming to NEMA AB1 HIC 50 kA at 600 V AC 50/60 Hz conforming to NEMA AB1 HIC
[Ics] rated service breaking capacity	Ics 130 kA 440 V AC 50/60 Hz conforming to IEC 60947-2 Ics 150 kA 220/240 V AC 50/60 Hz conforming to IEC 60947-2 Ics 150 kA 380/415 V AC 50/60 Hz conforming to IEC 60947-2 Ics 20 kA 660/690 V AC 50/60 Hz conforming to IEC 60947-2 Ics 50 kA 525 V AC 50/60 Hz conforming to IEC 60947-2 Ics 70 kA 500 V AC 50/60 Hz conforming to IEC 60947-2
Utilisation category	Category A
Trip unit name	TM-D
Trip unit technology	Thermal-magnetic

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Trip unit rating	80 A (40 °C)
Protection type	Overload protection (thermal) Protection of the fourth pole Short-circuit protection (magnetic)
Pollution degree	3 conforming to IEC 60947

Complementary

Control type	Toggle
Mounting mode	Fixed
Mounting support	Backplate
Upside connection	Front
Downside connection	Front
Mechanical durability	20000 cycles
Electrical durability	10000 cycles 440 V AC 50/60 Hz I _n conforming to IEC 60947-2 20000 cycles 440 V AC 50/60 Hz I _n /2 conforming to IEC 60947-2
Connection pitch	35 mm
Local signalling	Positive contact indication
Neutral protection setting	0.5 x I _r
Long time pick-up adjustment type I _r	Adjustable
Long time pick-up adjustment range	0.8...1 x I _n
Instantaneous pick-up adjustment type I _i	Fixed
Instantaneous pick-up adjustment range	1000 A
Height	161 mm
Width	140 mm
Depth	86 mm

Environment

Standards	IEC 60947-2
Product certifications	ASEFA ASTA KEMA LCIE
IP degree of protection	IP40 conforming to IEC 60529
IK degree of protection	IK07 conforming to EN 50102
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-50...85 °C

Contractual warranty

Warranty period	18 months
-----------------	-----------