

# Product data sheet

Specifications



Circuit breaker frame, ComPact NS1600bH, 70kA/415VAC, 1600A, fixed, manually operated, without trip unit, 4P

34004

! To be discontinued

! To be discontinued on: Apr 30, 2024

## Main

Range	ComPact
Range Of Product	ComPact NS1600b...3200
Device Short Name	Compact NS1600bH
Product Or Component Type	Basic frame
Device Application	Distribution
Number Of Poles	4P
Neutral Position	Left
[In] Rated Current	1600 A at 50 °C
[Ue] Rated Operational Voltage	690 V AC 50/60 Hz
Network Type	AC
Network Frequency	50/60 Hz
Suitability For Isolation	Yes conforming to EN/IEC 60947-2
Utilisation Category	Category A
[Icu] Rated Ultimate Short-Circuit Breaking Capacity	125 kA Icu at 220/240 V AC 50/60 Hz conforming to IEC 60947-2 85 kA Icu at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 85 kA Icu at 440 V AC 50/60 Hz conforming to IEC 60947-2
Performance Level	H 70 kA 415 V AC
Control Type	Toggle
Mounting Mode	Fixed

## Complementary

[Ui] Rated Insulation Voltage	800 V AC 50/60 Hz conforming to IEC 60947-2
[Uimp] Rated Impulse Withstand Voltage	8 kV conforming to IEC 60947-2
[Ics] Rated Service Short-Circuit Breaking Capacity	64 kA at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 (manual operation) 64 kA at 440 V AC 50/60 Hz conforming to IEC 60947-2 (manual operation) 94 kA at 220/240 V AC 50/60 Hz conforming to IEC 60947-2 (manual operation)
[Icw] Rated Short-Time Withstand Current	32 kA 3 s conforming to IEC 60947-2
Integral Instant Protection	130 kA
Mechanical Durability	5000 cycles conforming to IEC 60947-2
Electrical Durability	1000 cycles 690 V AC 50/60 Hz In conforming to IEC 60947-2 2000 cycles 440 V AC 50/60 Hz In conforming to IEC 60947-2 2000 cycles 690 V AC 50/60 Hz In/2 conforming to IEC 60947-2 3000 cycles 440 V AC 50/60 Hz In/2 conforming to IEC 60947-2

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Power Losses	84 W
Mounting Support	Backplate
Upside Connection	Front
Downside Connection	Front
Connection Pitch	115 mm
Protection Type	Without protection
Height (H)	350 mm
Width (W)	535 mm
Depth (D)	160 mm

## Environment

Standards	IEC 60947-2
Product Certifications	ASTA ASEFA LCIE
Pollution Degree	3 conforming to IEC 60947
Ip Degree Of Protection	IP40 conforming to IEC 60529
Ik Degree Of Protection	IK07 conforming to EN 50102
Ambient Air Temperature For Operation	-25...70 °C
Ambient Air Temperature For Storage	-50...85 °C

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	45.0 cm
Package 1 Width	60.0 cm
Package 1 Length	80.0 cm
Package 1 Weight	49.153 kg

## Contractual warranty

Warranty	18 months
----------	-----------

# Sustainability

**Green Premium™** label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

✓ Pvc Free

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	<a href="#">End of Life Information</a>
California Proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>