

Product data sheet

Specifications



Circuit breaker, ComPact NS630bH,
70kA/415VAC, Micrologic 5.0E trip
unit, 630A, fixed, 3 poles 3d

34421

⚠ To be discontinued on: Apr 30, 2024

⚠ To be discontinued

Main

| | |
|--|--|
| Range | ComPact |
| Product Name | ComPact NS |
| Range Of Product | ComPact NS630b...1600 |
| Device Short Name | Compact NS630bH |
| Product Or Component Type | Circuit breaker |
| Device Application | Distribution |
| Number Of Poles | 3P |
| Protected Poles Description | 3D |
| (In) Rated Current Up To 65 °C | 630 A at 50 °C |
| [Ue] Rated Operational Voltage | 690 V AC 50/60 Hz |
| Network Type | AC |
| Network Frequency | 50/60 Hz |
| Suitability For Isolation | Yes conforming to EN/IEC 60947-2 |
| Utilisation Category | Category B |
| [Icu] Rated Ultimate Short-Circuit Breaking Capacity | 42 kA Icu at 660/690 V AC 50/60 Hz conforming to IEC 60947-2 65 kA Icu at 440 V AC 50/60 Hz conforming to IEC 60947-2 70 kA Icu at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 85 kA Icu at 220/240 V AC 50/60 Hz conforming to IEC 60947-2 50 kA Icu at 500/525 V AC 50/60 Hz conforming to IEC 60947-2 |
| Performance Level | H 70 kA 415 V AC |
| Trip Unit Name | MicroLogic 5.0 E |
| Trip Unit Technology | Electronic |
| Trip Unit Protection Functions | LSI |
| Control Type | Toggle Rotary handle |
| Circuit Breaker Mounting Mode | Fixed |

Complementary

| | |
|--|---|
| [Ui] Rated Insulation Voltage | 800 V AC 50/60 Hz conforming to IEC 60947-2 |
| [Uimp] Rated Impulse Withstand Voltage | 8 kV conforming to IEC 60947-2 |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|--|--|
| [Ics] Rated Service Short-Circuit Breaking Capacity | 30 kA at 660/690 V AC 50/60 Hz conforming to IEC 60947-2 40 kA at 500/525 V AC 50/60 Hz conforming to IEC 60947-2 50 kA at 220/240 V AC 50/60 Hz conforming to IEC 60947-2 50 kA at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 50 kA at 440 V AC 50/60 Hz conforming to IEC 60947-2 |
| [Icw] Rated Short-Time Withstand Current | 19.2 kA 1 s conforming to IEC 60947-2 |
| Mechanical Durability | 10000 cycles |
| Electrical Durability | 2000 cycles at 690 V In 4000 cycles at 690 V In/2 5000 cycles at 440 V In 6000 cycles at 440 V In/2 |
| Power Losses | 10 W |
| Mounting Support | Backplate |
| Upside Connection | Front |
| Downside Connection | Front |
| Connection Pitch | 70 mm |
| Protection Type | L : for overload protection (long time) S : for short time short-circuit protection I : for instantaneous short-circuit protection |
| Trip Unit Rating | 630 A at 50 °C |
| Long-Time Pick-Up Adjustment Type Ir (Thermal Protection) | Adjustable 9 settings |
| [Ir] Long-Time Protection Pick-Up Adjustment Range | 0.4...1 x In |
| Long-Time Protection Delay Adjustment Type Tr | Adjustable 9 settings |
| [Tr] Long-Time Protection Delay Adjustment Range | 12.5...600 s at 1.5 x Ir 0.5...24 s at 6 x Ir 0.7...16.6 s at 7.2 x Ir |
| Thermal Memory | 20 mn |
| Short-Time Protection Pick-Up Adjustment Type Isd | Adjustable 9 settings |
| [Isd] Short-Time Protection Pick-Up Adjustment Range | 1.5...10 x Ir |
| Short-Time Protection Delay Adjustment Type Tsd | Adjustable |
| [Tsd] Short-Time Protection Delay Adjustment Range | 0.1...0.4 s I ² t=on 0...0.4 s I ² t=off |
| Instantaneous Protection Pick-Up Adjustment Type Ii | Adjustable |
| [Ii] Instantaneous Protection Pick-Up Adjustment Range | 2...15 x In Off |
| Earth-Leakage Protection | Without |
| Zone Selective Interlocking Zsi | With |
| Auxiliary Contact Composition | 1 NO/NC |
| Local Signalling | 4 LEDs (red) for fault indication 1 LED (yellow) for overload |
| Display Type | LCD display |
| Type Of Measurement | Energy meter |
| Width (W) | 210 mm |
| Height (H) | 327 mm |
| Depth (D) | 147 mm |
| Net Weight | 14 kg |

Environment

| | |
|---------------------------------------|--|
| Standards | EN/IEC 60947-2 |
| Product Certifications | ASTA ASEFA |
| Pollution Degree | 3 conforming to IEC 60947 |
| Ip Degree Of Protection | IP40 conforming to IEC 60529 |
| Ik Degree Of Protection | IK07 conforming to EN 50102 |
| Ambient Air Temperature For Operation | -25...70 °C |
| Ambient Air Temperature For Storage | -40...85 °C |
| Relative Humidity | 0...95 % |
| Operating Altitude | 0...2000 m without derating 2000 m...5000 m with derating |

Packing Units

| | |
|------------------------------|-----------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 37.0 cm |
| Package 1 Width | 39.5 cm |
| Package 1 Length | 23.0 cm |
| Package 1 Weight | 11.892 kg |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

| | |
|--------------------------|---|
| Reach Regulation | REACH Declaration |
| Eu Rohs Directive | Compliant with Exemptions |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information |
| Environmental Disclosure | Product Environmental Profile |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
| Circularity Profile | End of Life Information |