

Product data sheet

Specifications



Control unit MicroLogic 5.0A, MasterPact NW32H1, welded, specific SEG

34476

Main

Range	MasterPact
Range Of Product	MasterPact NW
Product Or Component Type	Control unit
Trip Unit Name	MicroLogic 5.0 A
Trip Unit Technology	Electronic
Device Application	Distribution
Number Of Poles	3P 4P
Protected Poles Description	4t 3t 3t + N/2
Trip Unit Protection Functions	Selective protection
Protection Type	for short time short-circuit protection for overload protection (long time) for instantaneous short-circuit protection
Trip Unit Rating	3200 A at 50 °C
Network Type	AC
Network Frequency	50/60 Hz
Circuit Breaker Mounting Mode	Fixed

Complementary

Long-Time Pick-Up Adjustment Type Ir (Thermal Protection)	Adjustable 9 settings
[Ir] Long-Time Protection Pick-Up Adjustment Range	0.4...1 x In
Long-Time Protection Delay Adjustment Type Tr	Adjustable 9 settings
[Tr] Long-Time Protection Delay Adjustment Range	0.7...16.6 s at 7.2 x Ir 0.7...24 s at 6 x Ir 12.5...600 s at 1.5 x Ir
Thermal Memory	20 mn
Short-Time Protection Pick-Up Adjustment Type Isd	Adjustable 9 settings
[Isd] Short-Time Protection Pick-Up Adjustment Range	1.5...10 x Ir
Short-Time Protection Delay Adjustment Type Tsd	Adjustable
[Tsd] Short-Time Protection Delay Adjustment Range	0...0.4 s I ² t=off 0.1...0.4 s I ² t=on
Instantaneous Protection Pick-Up Adjustment Type Ii	Adjustable 9 settings

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

[li] Instantaneous Protection Pick-Up Adjustment Range	2...15 x In Off
Earth-Leakage Protection	Without
Zone Selective Interlocking Zsi	With
Local Signalling	3 LEDs (red) for electrical fault 1 LED (red) for internal error
Display Type	Digital display
Type Of Measurement	Ammeter
Communication Of Data	Measurement readout Protection and alarm settings

Environment

Ambient Air Temperature For Operation	-25...70 °C
Ambient Air Temperature For Storage	-40...85 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.0 cm
Package 1 Width	6.0 cm
Package 1 Length	21.5 cm
Package 1 Weight	281.0 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	15
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	4.702 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov