

Product data sheet

Specifications



Circuit breaker frame, ComPacT
NS800L, 150kA/415VAC, 800A,
withdrawable, electrically operated,
without trip unit, 3P

33382

Main

Range	ComPacT
Range Of Product	ComPacT NS630b...1600 new generation
Device Short Name	Compact NS800L
Product Or Component Type	Basic frame
Device Application	Distribution
Number Of Poles	3P
[In] Rated Current	800 A at 50 °C
[Ue] Rated Operational Voltage	690 V AC 50/60 Hz
Network Type	AC
Network Frequency	50/60 Hz
Suitability For Isolation	Yes conforming to EN/IEC 60947-2
Utilisation Category	Category A
[Icu] Rated Ultimate Short-Circuit Breaking Capacity	130 kA Icu at 440 V AC 50/60 Hz conforming to IEC 60947-2 150 kA Icu at 220/240 V AC 50/60 Hz conforming to IEC 60947-2 150 kA Icu at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 100 kA Icu at 500/525 V AC 50/60 Hz conforming to IEC 60947-2
Performance Level	L 150 kA 415 V AC
Control Type	Electrically operated Motor mechanism with external connector
Mounting Mode	Drawout

Complementary

[Ui] Rated Insulation Voltage	1000 V AC 50/60 Hz conforming to IEC 60947-2
[Uimp] Rated Impulse Withstand Voltage	8 kV conforming to IEC 60947-2
[Ics] Rated Service Short-Circuit Breaking Capacity	100 kA at 500/525 V AC 50/60 Hz conforming to IEC 60947-2 (electrical operation) 130 kA at 440 V AC 50/60 Hz conforming to IEC 60947-2 (electrical operation) 150 kA at 220/240 V AC 50/60 Hz conforming to IEC 60947-2 (electrical operation) 150 kA at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 (electrical operation)
Mechanical Durability	10000 cycles conforming to IEC 60947-2
Electrical Durability	2000 cycles 690 V AC 50/60 Hz In conforming to IEC 60947-2 3000 cycles 440 V AC 50/60 Hz In conforming to IEC 60947-2 3000 cycles 690 V AC 50/60 Hz In/2 conforming to IEC 60947-2 4000 cycles 440 V AC 50/60 Hz In/2 conforming to IEC 60947-2
Power Losses	40 W
Mounting Support	Backplate
Connection Pitch	70 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Protection Type	Without protection
Height (H)	327 mm
Width (W)	210 mm
Depth (D)	147 mm

Environment

Standards	IEC 60947-2
Product Certifications	LCIE ASEFA ASTA
Pollution Degree	3 conforming to IEC 60947
Ip Degree Of Protection	IP40 conforming to IEC 60529
Ik Degree Of Protection	IK07 conforming to EN 50102
Ambient Air Temperature For Operation	-25...70 °C
Ambient Air Temperature For Storage	-50...85 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	36.0 cm
Package 1 Width	40.0 cm
Package 1 Length	23.0 cm
Package 1 Weight	16.664 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

✓ Pvc Free

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information