

Product data sheet

Specifications



base unit S10MX for Sepam series 40 - 24...250 V - with basic UMI

59600

⚠ Discontinued on: Jan 12, 2024

⚠ To be end-of-service on: Dec 31, 2030

⚠ Discontinued - Service only

Main

Range Of Product	Sepam series 40
Device Short Name	S10MX
User Machine Interface Type	Without

Complementary

Umi Control	Sepam reset Alarm acknowledgement
Display Resolution	128 x 64 pixels
Number Of Key	1
Local Signalling	2 LEDs for Sepam operating status (front face) 9 LEDs for indication of parameters (front face)
Output Type	Annunciation relay: 100...240 V AC 47.5...63 Hz continuous current: 2 A breaking capacity: 1 A cos ϕ > 0.3 Annunciation relay: 127 V DC continuous current: 2 A breaking capacity: 0.5 A L/R < 20 ms Annunciation relay: 220 V DC continuous current: 2 A breaking capacity: 0.15 A L/R < 20 ms Annunciation relay: 24 V DC continuous current: 2 A breaking capacity: 2 A L/R < 20 ms Annunciation relay: 48 V DC continuous current: 2 A breaking capacity: 1 A L/R < 20 ms Control relay: 100...240 V AC 47.5...63 Hz continuous current: 8 A breaking capacity: 5 A cos ϕ > 0.3 making capacity: < 15 A for 200 ms Control relay: 100...240 V AC 47.5...63 Hz continuous current: 8 A breaking capacity: 8 A resistive making capacity: < 15 A for 200 ms Control relay: 127 V DC continuous current: 8 A breaking capacity: 0.2 A L/R < 40 ms making capacity: < 15 A for 200 ms Control relay: 127 V DC continuous current: 8 A breaking capacity: 0.5 A L/R < 20 ms making capacity: < 15 A for 200 ms Control relay: 127 V DC continuous current: 8 A breaking capacity: 0.7 A resistive making capacity: < 15 A for 200 ms Control relay: 220 V DC continuous current: 8 A breaking capacity: 0.1 A L/R < 40 ms making capacity: < 15 A for 200 ms Control relay: 220 V DC continuous current: 8 A breaking capacity: 0.2 A L/R < 20 ms making capacity: < 15 A for 200 ms Control relay: 220 V DC continuous current: 8 A breaking capacity: 0.3 A resistive making capacity: < 15 A for 200 ms Control relay: 24 V DC continuous current: 8 A breaking capacity: 4 A L/R < 40 ms making capacity: < 15 A for 200 ms Control relay: 24 V DC continuous current: 8 A breaking capacity: 6 A L/R < 20 ms making capacity: < 15 A for 200 ms Control relay: 24 V DC continuous current: 8 A breaking capacity: 8 A resistive making capacity: < 15 A for 200 ms Control relay: 48 V DC continuous current: 8 A breaking capacity: 1 A L/R < 40 ms making capacity: < 15 A for 200 ms Control relay: 48 V DC continuous current: 8 A breaking capacity: 2 A L/R < 20 ms making capacity: < 15 A for 200 ms Control relay: 48 V DC continuous current: 8 A breaking capacity: 4 A resistive making capacity: < 15 A for 200 ms

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

[Us] Rated Supply Voltage	110/240 V AC 47.5...63 Hz tolerance: - 20...10 % deactivated consumption: < 6 VA maximum consumption: < 25 VA 24/250 V DC tolerance: - 20...10 % deactivated consumption: < 6 W maximum consumption: < 11 W
Supply Inrush Current	< 28 A for 0.1 ms at 24/250 V DC < 15 A at 110/240 V AC
Mounting Mode	Fixed
Mounting Support	Plate
Height	222 mm
Width	176 mm
Depth	129 mm
Net Weight	1.4 kg
Power Frequency Dielectric Withstand	2 kV during 1 min conforming to IEC 60255-5
[Uimp] Rated Impulse Withstand Voltage	5 kV (1.2/50 µs) conforming to IEC 60255-5
Mechanical Robustness	Earthquakes in operation (level: 2) : 1 Gn (vertical axes) conforming to IEC 60255-21-3 Earthquakes in operation (level: 2) : 2 Gn (horizontal axes) conforming to IEC 60255-21-3 Jolts de-energized (level: 2) : 20 Gn/16 ms conforming to IEC 60255-21-2 Shocks de-energized (level: 2) : 30 Gn/11 ms conforming to IEC 60255-21-2 Shocks in operation (level: 2) : 10 Gn/11 ms conforming to IEC 60255-21-2 Vibrations de-energized (level: 2) : 2 Gn, 10 Hz...150 Hz conforming to IEC 60255-21-1 Vibrations in operation (level: 2) : 1 Gn, 10 Hz...150 Hz conforming to IEC 60255-21-1 Vibrations in operation (level: Fc) : 2 Hz...13.2 Hz, a = +/- 1 mm conforming to IEC 60068-2-6

Environment

Standards	EN 50263 UL 508 CSA C22.2 No 94-M91 CSA C22.2 No 14-95 CSA C22.2 No 0.17-00
Product Certifications	UL 508 file N° 212533 C22.2 file N° 210625 CE
Fire Resistance	650 °C conforming to IEC 60695-2-11
Ip Degree Of Protection	Other panels: IP20 conforming to IEC 60529 Front panel: IP52 conforming to IEC 60529
Nema Degree Of Protection	Type 12 conforming to NEMA
Immunity To Microbreaks	10 ms

Electromagnetic Compatibility	<p>1 MHz damped oscillating wave: (immunity tests-conducted disturbances), III, 2.5 kV MC, 1 kV MD, conforming to IEC 60255-22-1</p> <p>Fast transient bursts: (immunity tests-conducted disturbances), A or B, 4kV, 2.5 kHz/ 2 kV, 5 kHz, conforming to IEC 60255-22-4</p> <p>Fast transient bursts: (immunity tests-conducted disturbances), IV, 4kV, 2.5 kHz, conforming to IEC 61000-4-4</p> <p>Immunity to magnetic fields at network frequency: (immunity tests-radiated disturbances), IV, 30 A/m (continuous)-300 A/m (13 s), conforming to IEC 61000-4-8</p> <p>Immunity to radiated fields: (immunity tests-radiated disturbances), III, 10 V/m, 80 MHz...2 GHz, conforming to IEC 61000-4-3</p> <p>Surges: (immunity tests-conducted disturbances), III, 2 kV MC, 1 kV MD, conforming to IEC 61000-4-5</p> <p>1 MHz damped oscillating wave: (immunity tests-conducted disturbances), 2.5 kV MC and MD, conforming to ANSI C37.90.1</p> <p>100 kHz damped oscillating wave: (immunity tests-conducted disturbances), 2.5 kV MC, 1 kV MD, conforming to IEC 61000-4-12</p> <p>Conducted disturbance emission: (emission tests), conforming to IEC 60255-25</p> <p>Conducted disturbance emission: (emission tests), B, conforming to EN 55022</p> <p>Disturbing field emission: (emission tests), conforming to IEC 60255-25</p> <p>Disturbing field emission: (emission tests), A, conforming to EN 55022</p> <p>Electrostatic discharge: (immunity tests-radiated disturbances), 8 kV air, 4 kV contact, conforming to ANSI C37.90.3</p> <p>Electrostatic discharge: (immunity tests-radiated disturbances), 8 kV air, 6 kV contact, conforming to IEC 60255-22-2</p> <p>Fast transient bursts: (immunity tests-conducted disturbances), 4kV, 2.5 kHz, conforming to ANSI C37.90.1</p> <p>Immunity to conducted RF disturbances: (immunity tests-conducted disturbances), 10 V, conforming to IEC 60255-22-6</p> <p>Immunity to radiated fields: (immunity tests-radiated disturbances), 10 V/m, 80 MHz... 1 GHz, conforming to IEC 60255-22-3</p> <p>Immunity to radiated fields: (immunity tests-radiated disturbances), 35 V/m, 25 MHz... 1 GHz, conforming to ANSI C37.90.2 (1995)</p> <p>Voltage interruptions: (immunity tests-conducted disturbances), 100 %, 20 ms, conforming to IEC 60255-11</p>
-------------------------------	--

Climatic Withstand	<p>Continuous exposure to damp heat (in operation) : Ca: 10 days, 93 % RH, 40 °C (104 °F) conforming to IEC 60068-2-3</p> <p>Continuous exposure to damp heat (in storage) : Ca: 56 days, 93 % RH, 40 °C (104 °F) conforming to IEC 60068-2-3</p> <p>Exposure to cold (in operation) : Ad: - 25 °C (- 13 °F) conforming to IEC 60068-2-1</p> <p>Exposure to cold (in storage) : Ab: - 25 °C (- 13 °F) conforming to IEC 60068-2-1</p> <p>Exposure to dry heat (in operation) : Bd: 70 °C (158 °F) conforming to IEC 60068-2-2</p> <p>Exposure to dry heat (in storage) : Bb: 70 °C (158 °F) conforming to IEC 60068-2-2</p> <p>Influence of corrosion/gaz test 2 (in operation) : C: 21 days, 75 % RH, 25 °C (- 13 °F), 0.5 ppm H2S, 1 ppm SO2 conforming to IEC 60068-2-60</p> <p>Temperature variation with specified variation rate (in operation) : Nb: - 25 °C to 70 °C (- 13 °F to 158 °F) 5 °C/min (41 °F/min) conforming to IEC 60068-2-14</p> <p>Influence of corrosion/gaz test 4 (in operation) : 21 days, 75 % RH, 25 °C, 0.01 ppm H2S, 0.2 ppm SO2, 0.02 ppm NO2, 0.01 ppm Cl2 conforming to IEC 60068-2-60</p> <p>Salt mist (in operation) : Kb/2 conforming to IEC 60068-2-52</p>
--------------------	--

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	12.0 cm
Package 1 Width	28.0 cm
Package 1 Length	28.0 cm
Package 1 Weight	1.387 kg
Unit Type Of Package 2	S03
Number Of Units In Package 2	3
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	4.874 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

 Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information