

# Product data sheet

Specifications



## transformer - T42 - Sepam series 40

59684

⚠ Discontinued on: Jan 12, 2024

⚠ To be end-of-service on: Dec 31, 2030

⚠ Discontinued - Service only

### Main

Relay Application	Transformer
Range Of Product	Sepam series 40
Device Short Name	T42
Control And Monitoring Type	Latching/acknowledgement ANSI code: 86 Logic discrimination ANSI code: 68 (option) Switching of groups of settings Annunciation ANSI code: 30 Circuit breaker/contactors control ANSI code: 94/69 Logic equation editor 100 operators
Metering Type	Phase current I1, I2, I3 RMS, residual current I0 Demand current I1, I2, I3, peak demand current IM1, IM2, IM3 Temperature (option) Voltage U21, U32, U13, V1, V2, V3, residual voltage V0 Frequency Positive sequence voltage Vd/rotation direction-negative sequence voltage Vi Active, reactive, apparent power P,Q,S-peak demand power PM, QM, power factor Calculated active and reactive energy (+/- W.h, +/- VAR.h) Active and reactive energy by pulse counting (+/- W.h, +/- VAR.h) (option)
Network And Machine Diagnosis Type	Unbalance ratio/negative sequence current Ii Disturbance recording Thermal capacity used Remaining operating time before overload tripping Waiting time after overload tripping Running hours counter/operating time Tripping context Phase displacement
Switchgear Diagnosis Type	Cumulative breaking current Trip circuit supervision (option) Number of operations, operating time charging time (option) CT/VT supervision ANSI code: 60FL

### Complementary

Type Of Measurement	Frequency Energy Temperature Voltage Power factor Peak demand power Power (P,Q) Current
---------------------	--

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Protection Type	Thermal overload protection ANSI code: 49RMS (2) Thermostat / buchholz ANSI code: 26/63 (option) Neutral voltage displacement ANSI code: 59N (2) Breaker failure ANSI code: 50BF (1) Undervoltage protection ANSI code: 27/27S (2) Overvoltage protection ANSI code: 59 (2) Directional earth fault ANSI code: 67N/67NC (2) Directional phase overcurrent ANSI code: 67 (2) Temperature monitoring (8 or 16 RTDs) ANSI code: 38/49T (option) Phase overcurrent ANSI code: 50/51 (4) Earth fault/sensitive earth fault ANSI code: 50N/51N (4) Earth fault/sensitive earth fault ANSI code: 50G/51G (4) Negative sequence/unbalance ANSI code: 46 (2) Negative sequence overvoltage ANSI code: 47 (1) Overfrequency ANSI code: 81H (2) Underfrequency ANSI code: 81L (4)
Communication Port Protocol	Measurement readout ( option ) : Modbus Remote indication and time tagging of events ( option ) : Modbus Remote control orders ( option ) : Modbus Remote protection setting ( option ) : Modbus Transfer of disturbance recording data ( option ) : Modbus
Input Output Max Capacity	10 inputs + 8 outputs
Communication Compatibility	IEC 61850 Modbus RTU IEC 60870-5-103 DNP3 Modbus TCP/IP
User Machine Interface Type	Advanced Without Remote

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.1 cm
Package 1 Width	0.1 cm
Package 1 Length	0.2 cm
Package 1 Weight	1.0 g

## Sustainability




**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance

	Reach Free Of Svhc	
	Mercury Free	
	Rohs Exemption Information	<a href="#">Yes</a>
<hr/>		
Reach Regulation		<a href="#">REACH Declaration</a>
<hr/>		
Eu Rohs Directive		Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
<hr/>		
China Rohs Regulation		<a href="#">China RoHS declaration</a>
<hr/>		