



Main

| | |
|---------------------------|--------------------|
| Range | PratiKa |
| Product or component type | Interlocked socket |
| Device short name | Unika socket |
| Plug, socket category | Low voltage |
| Poles description | 2P + E |
| Network type | AC |
| Outlet standard | Industrial |

Complementary

| | |
|--------------------------------|--|
| Mounting mode | Wall-mounted |
| [In] rated current | 16 A |
| [Ue] rated operational voltage | 100...130 V |
| Network frequency | 50/60 Hz |
| Ground lug clockwise position | 4 h |
| Protection type | Fuse |
| Fuse type | Cylindrical |
| Fuse size | 10.3 x 38 mm |
| Plug, socket material | Self-extinguishing engineering polymer housing : |
| Contacts material | Nickel plated brass sleeves : |
| Connections - terminals | Captive screws |
| Cable cross section | <= 10 mm ² |
| Cable outer diameter | <= 25 mm |
| Cable entry | Cable gland |
| Thread type | Pg 21 |
| Product weight | 1.04 kg |
| Base dimension | 103 x 255 mm |
| Height | 255 mm |
| Width | 103 mm |
| Depth | 150 mm |
| Colour | Grey (RAL 7035) |
| Voltage colour | Yellow |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

| | |
|---------------------------------------|--|
| Standards | IEC 60309-1 IEC 60309-2 |
| IP degree of protection | IP44 conforming to IEC 60529 |
| IK degree of protection | IK09 conforming to EN 62262 |
| Fire resistance | 750 °C conforming to IEC 60695-2-11 |
| Relative humidity | 50 % (40 °C) 70 % (30 °C) 90 % (20 °C) |
| Ambient air temperature for operation | 35 °C (86400 s) -25...40 °C |

Contractual warranty

| | |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|