

Product data sheet

Specifications



Wibe - cover 64-800 - 2 m - steel hot-dip galvanized

782567

⚠ Discontinued on: Dec 31, 2016

⚠ End-of-service on: Mar 10, 2017

⚠ Discontinued

Main

Range	Wibe
Product	Wibe Cable Ladders
Product Or Component Type	Cover
Device Short Name	64
Mounting Location	Area with high level of environmental corrosion, humidity and airborne pollution industrial and coastal areas, chemical plants

Complementary

Product Destination	800 mm width vertical cable ladder
Material With Surface Treatment	Steel, hot-dip galvanized
Corrosion Class	C3/C4
Length	2000 mm
Height	10 mm
Width	801 mm
Net Weight	1660 kg / set of 100

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1 cm
Package 1 Width	80.1 cm
Package 1 Length	200 cm
Package 1 Weight	16.6 kg

Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations