

Product data sheet

Specifications

Kaedra - cable gland - PG13,5



83993

Main

| | |
|------------------------------------|-------------------|
| Range Of Product | Kaedra |
| Product Or Component Type | Cable gland |
| Accessory / Separate Part Category | Cabling accessory |

Complementary

| | |
|------------------|---------|
| Cable Gland Type | Pg 13.5 |
| Net Weight | 0.01 kg |

Environment

| | |
|---------------------------------------|-------------------------------------|
| Fire Resistance | 850 °C conforming to IEC 60695-2-11 |
| Ip Degree Of Protection | IP55 conforming to IEC 60529 |
| Ik Degree Of Protection | IK08 conforming to EN 62262 |
| Ambient Air Temperature For Operation | -25...40 °C |

Packing Units

| | |
|------------------------------|----------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 2.6 cm |
| Package 1 Width | 2.8 cm |
| Package 1 Length | 3.7 cm |
| Package 1 Weight | 14.0 g |
| Unit Type Of Package 2 | S04 |
| Number Of Units In Package 2 | 300 |
| Package 2 Height | 30.0 cm |
| Package 2 Width | 40.0 cm |
| Package 2 Length | 60.0 cm |
| Package 2 Weight | 4.763 kg |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability





Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

| | | |
|---|----------------------------|---|
|  | Reach Free Of Svhc | |
|  | Toxic Heavy Metal Free | |
|  | Mercury Free | |
|  | Rohs Exemption Information | Yes |
| | | |
| Reach Regulation | | REACH Declaration |
| | | |
| Eu Rohs Directive | | Compliant EU RoHS Declaration |
| | | |
| China Rohs Regulation | | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) |
| | | |
| Weee | | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |